

ST-REL3-KG120/21/SO46 - Relay connectors



2833026

<https://www.phoenixcontact.com/us/products/2833026>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in relay interface for protection against interference on the control side, with soldered-in miniature switching relay, contacts (AgNi): medium to large loads, 1 changeover contact, input voltage 120 V AC

The figure shows version ST-REL 3-KG 24/21/SO 46

Your advantages

- Use of AC output cards, resulting in residual AC currents
- Resistant to interference currents
- Applications with long control lines
- High relay release voltage

Commercial data

Item number	2833026
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK6122
GTIN	4017918118204
Weight per piece (including packing)	41.42 g
Weight per piece (excluding packing)	41.42 g
Customs tariff number	85364900
Country of origin	DE

ST-REL3-KG120/21/SO46 - Relay connectors



2833026

<https://www.phoenixcontact.com/us/products/2833026>

Technical data

Product properties

Product type	Relay Module
Mechanical service life	approx. 2×10^7 cycles

Insulation characteristics

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	01.04.2026
------------------------------	------------

Electrical properties

Maximum power dissipation for nominal condition	2.28 W
Test voltage (Winding/contact)	2.5 kV AC (50 Hz, 1 min., winding/contact)

Input data

Coil side

Nominal input voltage U_N	120 V AC
Input voltage range	102 V AC ... 132 V AC
Input voltage range in reference to U_N	0.85 ... 1.1
Drive and function	monostable
Typical input current at U_N	19 mA
Typical response time	8 ms
Typical release time	11 ms
Protective circuit	Bridge rectifier; Bridge rectifier Surge protection; Varistor RC element; RC element
Operating voltage display	Yellow LED

Output data

Switching

Contact switching type	Single contact, 1 changeover contact
Type of switch contact	Single contact
Contact material	AgNi
Maximum switching voltage	250 V AC/DC
Limiting continuous current	6 A
Maximum inrush current	8 A
Interrupting rating (ohmic load) max.	95 W (at 24 V DC) 50 W (at 48 V DC) 45 W (at 60 V DC)

ST-REL3-KG120/21/SO46 - Relay connectors



2833026

<https://www.phoenixcontact.com/us/products/2833026>

	35 W (at 110 V DC)
	55 W (at 220 V DC)
	2000 VA (for 250 V AC)

Dimensions

Width	20.8 mm
Height	42.5 mm
Depth	112 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	EN 50178

Mounting

Mounting position	any
-------------------	-----


ST-REL3-KG120/21/SO46 - Relay connectors



2833026

<https://www.phoenixcontact.com/us/products/2833026>

Drawings



Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com