EB 80- DIK BU - Insertion bridge

2715940

https://www.phoenixcontact.com/us/products/2715940

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insertion bridge, pitch: 6.2 mm, number of positions: 80, color: blue

Commercial data

Item number	2715940
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918061692
Weight per piece (including packing)	36 g
Weight per piece (excluding packing)	34.78 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Insertion bridge
Number of positions	80
Pitch	6.2 mm
Potentials	80

Dimensions

Pitch	6.2 mm

Material specifications

Color	blue (RAL 5015)
Material	Cu
Insulating material	PA

Mounting

Mounting type	Screw mounting

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.313 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com