

IBS IP CDIO/R 24-8/SF - I/O module



2719564

<https://www.phoenixcontact.com/us/products/2719564>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Digital input/output module, for use on robots, IP65 degree of protection, 8 inputs, 24 V DC, 4-conductor connection technology or 8 outputs, 24 V DC, 0.5 A, 3-conductor connection technology, connection of additional signals via the back of the module

The figure shows version IBS IP CDIO/R 24-8

Product description

The IBS IP CDIO/R 24... modules are available as an input/output unit for the robot concept. The metal housing allows them to be used in welding applications. The module can be used directly on the welding transformer if it is mounted on a terminal box. The modules are connected via a 17-pin circular connector. In addition to the INTERBUS and power supply lines, this connector also carries two further signal lines for constant current regulation (CCR) and for secondary circuit monitoring (SCM). These signals are looped in on the underside of the .../SF devices and are needed at the welding current controller for control and monitoring tasks.

Two module types are available:

The IBS IP CDIO 24-8 ... module has 8 channels that can be used either as inputs or as outputs.

The IBS IP CDIO 24-12/4/8 .. module has 12 inputs and 8 outputs.

Your advantages


- Degree of protection IP65
- Electrical isolation of I/O and bus logic

Commercial data

Item number	2719564
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN16
Product key	DR1A23
GTIN	4017918241650
Weight per piece (including packing)	686.7 g
Weight per piece (excluding packing)	681 g
Customs tariff number	85176200
Country of origin	DE

Technical data

Dimensions

Dimensional drawing		
Width		54 mm
Height		150 mm
Depth		62 mm

Interfaces

Installation remote bus

Transmission speed	500 Mbps
--------------------	----------

System properties

Local diagnostics

Error messages via the bus	Short-circuit or overload of the initiator power supply
	Short-circuit or overload of the output

Input data

Digital

Number of inputs	8
Input voltage	24 V DC
Input voltage range "0" signal	-30 V ... 5 V
Input voltage range "1" signal	13 V ... 30 V
Protective circuit	Short-circuit protection, polarity reversal protection
Connection technology	4-conductor

Output data

Digital

Number of outputs	7
Protective circuit	Short-circuit protection, polarity reversal protection

Product properties

Product type	I/O component
Type	Block design

2719564

<https://www.phoenixcontact.com/us/products/2719564>

Electrical properties

Supply

Supply voltage	24 V DC
Supply voltage range	18.5 V ... 30.5 V (including ripple)
Residual ripple	3.6 V _{PP}

Connection data

Connection method	M17 circular connector
-------------------	------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
----------------------	------

Mounting

Mounting type	Panel mounting
---------------	----------------

IBS IP CDIO/R 24-8/SF - I/O module


2719564

<https://www.phoenixcontact.com/us/products/2719564>



Drawings

Dimensional drawing




IBS IP CDIO/R 24-8/SF - I/O module

2719564

<https://www.phoenixcontact.com/us/products/2719564>

Connection diagram



a = female n

b = male n+1

c = sensor sockets 1, 3, 5, 7

d = sensor sockets 2, 4, 6, 8

IBS IP CDIO/R 24-8/SF - I/O module

2719564

<https://www.phoenixcontact.com/us/products/2719564>



Classifications

UNSPSC

UNSPSC 21.0	32151602
-------------	----------

2719564

<https://www.phoenixcontact.com/us/products/2719564>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com