

UM122-2FLK14/PI-ES/4/OUT/S7 - Basic terminal block



2835642

<https://www.phoenixcontact.com/us/products/2835642>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Analog out motherboard for S7-300, to hold PI-C-UI-UI-AO, mounting on NS 32, or NS 35/7.5.



Commercial data

Item number	2835642
Packing unit	1 pc
Sales key	C430
Product key	DK1XXX
GTIN	4017918827274
Weight per piece (including packing)	240.3 g
Weight per piece (excluding packing)	164.7 g
Customs tariff number	85389099
Country of origin	DE

2835642

<https://www.phoenixcontact.com/us/products/2835642>

Technical data


Product properties

Product type	Module carrier
Application	Base element

Electrical properties

Nominal voltage U_N	20 V DC ... 35 V DC
Nominal current I_N	60 mA (max. current consumption)
Reverse polarity protection	yes

Dimensions

Dimensional drawing	
Width	58.6 mm
Height	127.5 mm
Depth	82.6 mm
Depth NS 35/7,5	142.5 mm (with NS 35/7.5 coupling connector)
Depth NS 32	147.5 mm (with NS 32 coupling connector)
Depth NS 35/15	150 mm (with NS 35/15 coupling connector)

Material specifications

Color	green (RAL 6021)
Flammability rating according to UL 94	V0
Housing insulation material	Polyamide PA non-reinforced, polycarbonate PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C

Approvals


CE

Certificate	CE-compliant
-------------	--------------


Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Drawings



Dimensional drawing



UM122-2FLK14/PI-ES/4/OUT/S7 - Basic terminal block



2835642

<https://www.phoenixcontact.com/us/products/2835642>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------