

IB IL RS 485/422 - Inline function terminal



2836793

<https://www.phoenixcontact.com/us/products/2836793>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline RS-485/422 function terminal block, without accessories, 1 serial input and output channel

Product description

The terminal is designed for use within an Inline station. The terminal can be used to operate standard I/O devices with serial interfaces on a bus system.

Your advantages

- Diagnostic and status indicators
- 4 kbyte receive buffer and 1 kbyte transmit buffer
- Number of data bits, stop bits and parity can be set
- Transmission speed can be set up to 38400 bps
- 1 serial input and output channel as RS-485 or RS-422 version
- Various protocols supported

Commercial data

Item number	2836793
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRI151
GTIN	4017918160814
Weight per piece (including packing)	131.3 g
Weight per piece (excluding packing)	131.3 g
Customs tariff number	85389091
Country of origin	DE

Technical data

Product properties

Type	modular
Number of plugs	2

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

System properties

Module

ID code (dec.)	220
ID code (hex)	DC
Length code (hex)	01
Length code (dec)	01
Process data channel	16 bit
Input address area	2 Byte
Output address area	2 Byte
Register length	48 bit
Required parameter data	27 Byte

Electrical properties

Test section	5 V supply, incoming remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	5 V supply, outgoing remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	RS-485/422 interface / 7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	RS-485/422 interface / 24 V supply (I/O) 500 V AC 50 Hz 1 min
	RS-485/422 interface/functional ground 500 V AC 50 Hz 1 min
	7.5 V supply (bus logics)/24 V supply (I/O) 500 V AC 50 Hz 1 min
	7.5 V supply (bus logic)/functional ground 500 V AC 50 Hz 1 min
24 V supply (I/O) / functional ground 500 V AC 50 Hz 1 min	

Supply

I/O voltage	24 V DC (via voltage jumper)
I/O voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Residual ripple	± 1.2 V
Typical current consumption	170 mA

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 260 mA (all connections of the serial interface are short-circuited)
	typ. 170 mA

IB IL RS 485/422 - Inline function terminal

2836793

<https://www.phoenixcontact.com/us/products/2836793>

Connection data

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16

Interfaces


Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps

RS-485 half duplex or RS-422 full duplex (as alternative only)

Connection method	Spring-cage connection
Transmission speed	110 bps ... 38400 bps (configurable)
Transmission physics	Copper
Data bits	7 or 8
Stop bits	1 or 2
Input buffer	4 kByte
Output buffer	1 kByte

Dimensions

Dimensional drawing	
Width	24.4 mm
Height	119.8 mm
Depth	71.5 mm

Material specifications

Color	green
-------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	75 % ... 85 % (in the range of -25°C ... +55°C, appropriate measures against increased humidity (> 85%) must be taken.)

IB IL RS 485/422 - Inline function terminal



2836793

<https://www.phoenixcontact.com/us/products/2836793>

Permissible humidity (storage/transport)	75 % ... 85 % (Slight temporary condensation may sometimes appear on the housing, e.g. when the terminal block is brought out of a vehicle into an enclosed room.)
--	--

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL RS 485/422 - Inline function terminal

2836793


<https://www.phoenixcontact.com/us/products/2836793>

Drawings

Dimensional drawing



Connection diagram




IB IL RS 485/422 - Inline function terminal

2836793

<https://www.phoenixcontact.com/us/products/2836793>

Block diagram



IB IL RS 485/422 - Inline function terminal



2836793

<https://www.phoenixcontact.com/us/products/2836793>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com