

PT 2-TELE-ST - Surge protection plug



2838733

<https://www.phoenixcontact.com/us/products/2838733>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protection plug for base element, for protecting a double conductor of analog telecommunication interfaces.

Commercial data

Item number	2838733
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	CL03
Product key	CL3121
GTIN	4046356044677
Weight per piece (including packing)	28.8 g
Weight per piece (excluding packing)	28.94 g
Customs tariff number	85363010
Country of origin	DE

PT 2-TELE-ST - Surge protection plug

2838733

<https://www.phoenixcontact.com/us/products/2838733>

Technical data

Product properties

Product type	Surge protection for information technology
Product family	PLUGTRAB PT
IEC test classification	B2
	C1
	C2
	C3
	D1
Type	Male
Number of positions	2
Surge protection fault message	none
Wire pairs per module	1

Insulation characteristics

Overvoltage category	III
Pollution degree	2


Electrical properties

Nominal voltage U_N	185 V DC
	130 V AC

Connection data

Connection method	pluggable
-------------------	-----------

Dimensions

Dimensional drawing	
Width	17.7 mm
Height	45 mm
Depth	52 mm
Horizontal pitch	1 Div.
Complete module width	17.7 mm
Complete module height	90 mm
Complete module depth	65.5 mm

Material specifications

Color	black (RAL 9005)
	copper color
Flammability rating according to UL 94	V-0

PT 2-TELE-ST - Surge protection plug



2838733

<https://www.phoenixcontact.com/us/products/2838733>

Housing material	PA 6.6
------------------	--------

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Direction of action	Line-Line & Line-Earth Ground
Nominal voltage U_N	185 V DC
	130 V AC
Maximum continuous operating voltage U_C	185 V DC
	130 V AC
Rated current	450 mA AC (45 °C)
	130 mA DC (45 °C)
Operating effective current I_C at U_C	$\leq 10 \mu\text{A}$
Protective conductor current I_{PE}	$\leq 10 \mu\text{A}$
Nominal discharge current I_n (8/20) μs (line-line)	10 kA
Nominal discharge current I_n (8/20) μs (line-ground)	10 kA
Pulse discharge current I_{imp} (10/350) μs (line-line)	1 kA
Pulse discharge current I_{imp} (10/350) μs (line-earth)	1 kA
Total discharge current I_{Total} (8/20) μs	18 kA
Max. discharge current I_{max} (8/20) μs maximum (line-earth)	18 kA
Nominal pulse current I_{an} (10/700) μs (line-line)	100 A
Nominal pulse current I_{an} (10/700) μs (line-earth)	100 A
Output voltage limitation at 1 kV/ μs (line-line) spike	$\leq 300 \text{ V}$
Output voltage limitation at 1 kV/ μs (line-earth) spike	$\leq 300 \text{ V}$
Output voltage limitation at 1 kV/ μs (line-line) static	$\leq 300 \text{ V}$
Output voltage limitation at 1 kV/ μs (line-earth) static	$\leq 300 \text{ V}$
Residual voltage at I_n (conductor-conductor)	$\leq 160 \text{ V}$ (C2 - 10 kV / 5 kA)
Residual voltage at I_n (conductor-ground)	$\leq 200 \text{ V}$ (C2 - 10 kV / 5 kA)
Voltage protection level U_p (line-line)	$\leq 250 \text{ V}$ (B2 - 1 kV / 25 A)
	$\leq 300 \text{ V}$ (B2 - 4 kV / 100 A)
	$\leq 270 \text{ V}$ (C1 - 1 kV / 500 A)
	$\leq 300 \text{ V}$ (C2 - 2 kV/1 kA)
	$\leq 320 \text{ V}$ (C2 - 4 kV / 2 kA)
	$\leq 330 \text{ V}$ (C2 - 10 kV / 5 kA)
Voltage protection level U_p (line-earth)	$\leq 250 \text{ V}$ (B2 - 1 kV / 25 A)
	$\leq 300 \text{ V}$ (B2 - 4 kV / 100 A)
	$\leq 270 \text{ V}$ (C1 - 1 kV / 500 A)
	$\leq 300 \text{ V}$ (C2 - 2 kV/1 kA)
	$\leq 320 \text{ V}$ (C2 - 4 kV / 2 kA)
	$\leq 330 \text{ V}$ (C2 - 10 kV / 5 kA)
Response time t_A (line-line)	$\leq 500 \text{ ns}$
Response time t_A (line-earth)	$\leq 500 \text{ ns}$

PT 2-TELE-ST - Surge protection plug



2838733

<https://www.phoenixcontact.com/us/products/2838733>

Input attenuation aE, sym.	typ. 0.4 dB (≤ 5 MHz / 100 Ω)
Cut-off frequency f_g (3 dB), sym. in 100 Ω system	typ. 20 MHz
Capacity (Core-Core)	typ. 30 pF (f=1 MHz / $V_R=0$ V)
Capacity (Core-Earth)	typ. 30 pF (f=1 MHz / $V_R=0$ V)
Surge protection fault message	none
Impulse durability (line-line)	B2 - 4 kV / 100 A
	C1 - 1 kV / 500 A
	C2 - 10 kV / 5 kA
	C3 - 25 A
	D1 - 1 kA
Impulse durability (line-earth)	B2 - 4 kV / 100 A
	C1 - 1 kV / 500 A
	C2 - 10 kV / 5 kA
	C3 - 25 A
	D1 - 1 kA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Standards and regulations

Standards/specifications	IEC 61643-21
Note	2000
Standards/specifications	EN 61643-21
Note	2002

Mounting

Mounting type	on base element
---------------	-----------------

PT 2-TELE-ST - Surge protection plug

2838733

<https://www.phoenixcontact.com/us/products/2838733>


Drawings

Dimensional drawing



The figure shows the complete module consisting of a base element and connector

Circuit diagram



PT 2-TELE-ST - Surge protection plug



2838733

<https://www.phoenixcontact.com/us/products/2838733>

Classifications

ECLASS

ECLASS-13.0	27171503
ECLASS-15.0	27171503

ETIM

ETIM 10.0	EC001466
-----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

PT 2-TELE-ST - Surge protection plug



2838733

<https://www.phoenixcontact.com/us/products/2838733>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a019aefc-4f31-4732-92b0-bf6a402b9381

EF3.1 Climate Change

CO2e kg	0.893 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com