

IBS RL 24 ADAP-T/LK - Adapter set

2725037

<https://www.phoenixcontact.com/us/products/2725037>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

INTERBUS Rugged Line adapter for converting the copper wire remote bus to a fiber optic remote bus



The figure shows different versions of the bus connector with accessories

Your advantages

- The adapters can be used to switch between fiber optics and copper as the transmission medium or to convert to an M23 connector.

Commercial data

Item number	2725037
Packing unit	1 pc
Sales key	DR03
Product key	DRI5Z1
GTIN	4017918185442
Weight per piece (including packing)	184 g
Weight per piece (excluding packing)	184 g
Customs tariff number	85366990
Country of origin	DE

IBS RL 24 ADAP-T/LK - Adapter set

2725037

<https://www.phoenixcontact.com/us/products/2725037>



Technical data

Product properties

Product type	Plug
--------------	------

IBS RL 24 ADAP-T/LK - Adapter set

2725037

<https://www.phoenixcontact.com/us/products/2725037>



Classifications

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

IBS RL 24 ADAP-T/LK - Adapter set



2725037

<https://www.phoenixcontact.com/us/products/2725037>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com