


# IB IL 24 DI 8 - Digital module

2726227

<https://www.phoenixcontact.com/us/products/2726227>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Digital input terminal, Digital inputs: 8 (IEC 61131-2 type 1), connection technology: 2-, 3-, 4-conductor

## Product description

The terminal is designed for use within an Inline station. It is used to acquire digital signals.

## Your advantages

- Connection of sensors in 2-, 3-, and 4-conductor technology
- Diagnostic and status indicators
- Maximum permissible load current from the terminal: 2 A
- Maximum permissible load current per sensor: 250 mA
- 8 digital inputs

## Commercial data

Item number	2726227
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRI131
GTIN	4017918162856
Weight per piece (including packing)	142.95 g
Weight per piece (excluding packing)	109.81 g
Customs tariff number	85389091
Country of origin	DE

## Technical data

### Product properties

Type	modular
No. of channels	8

### System properties

#### Module

ID code (dec.)	190
ID code (hex)	BE
Length code (hex)	81
Length code (dec)	129
Process data channel	8 bit
Input address area	1 Byte
Output address area	0 Byte
Register length	8 bit
Required parameter data	1 Byte

### Electrical properties

#### Potentials: Communications power ( $U_L$ )

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 50 mA

#### Potentials: Segment circuit supply ( $U_S$ )

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 2 A

#### Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logics)/24 V supply (I/O)	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply (I/O) / functional ground	500 V AC, 50 Hz, 1 min

### Input data

#### Digital:

Input name	Digital inputs
Number of inputs	8 (IEC 61131-2 type 1)
Connection method	Spring-cage connection
Connection technology	2-, 3-, 4-conductor
Input voltage	24 V DC (via voltage jumper)
Input voltage range "0" signal	-3 V DC ... 5 V DC

# IB IL 24 DI 8 - Digital module

2726227

<https://www.phoenixcontact.com/us/products/2726227>

Input voltage range "1" signal	15 V DC ... 30 V DC
Typical response time	< 1 ms
Protective circuit	Short-circuit and overload protection

## Connection data

### Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16

## Interfaces

### Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps

## Dimensions

Dimensional drawing	
Width	48.8 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IB IL 24 DI 8 - Digital module


2726227

<https://www.phoenixcontact.com/us/products/2726227>




## Drawings

Dimensional drawing



Connection diagram



# IB IL 24 DI 8 - Digital module



2726227

<https://www.phoenixcontact.com/us/products/2726227>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)