

IBS IP CDIO/R 24-12/4/8-SF - I/O module



2730077

<https://www.phoenixcontact.com/us/products/2730077>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows version IBS IP CDIO/R 24-8

Digital input/output module, for use on robots, IP65 degree of protection, 12 inputs, 24 V DC, 4-conductor connection technology and 4 outputs, 24 V DC, 0.5 A/2 A, 3-conductor connection technology, connection of additional signals via the back of the module

Your advantages

- 4 digital outputs
- Diagnostic and status indicators
- 12 digital inputs

Commercial data

Item number	2730077
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN16
Product key	DRIA23
GTIN	4017918437312
Weight per piece (including packing)	659.4 g
Weight per piece (excluding packing)	651 g
Customs tariff number	85176200
Country of origin	DE

Technical data

Interfaces

Installation remote bus

Transmission speed	500 Mbps
--------------------	----------

System properties

Local diagnostics

Error messages via the bus	Short-circuit or overload of the initiator power supply
	Short-circuit or overload of the output
	Undervoltage from US1 / US2

Input data

Digital

Number of inputs	12
Input voltage	24 V DC
Input voltage range "0" signal	-30 V ... 5 V
Input voltage range "1" signal	13 V ... 30 V
Connection technology	4-conductor

Output data

Digital

Number of outputs	4
Protective circuit	Short-circuit protection, polarity reversal protection

Product properties

Product type	I/O component
Type	Block design

Electrical properties

Test section	Supply voltage US1; sensor supply 500 V AC 50 Hz 1 min
	Supply voltage US2 500 V AC 50 Hz 1 min
	Bus logic, incoming and outgoing remote bus 500 V AC 50 Hz 1 min

Supply

Supply voltage	24 V DC
Supply voltage range	18.5 V ... 32 V (including ripple)
Residual ripple	3.6 V _{PP}

Connection data

Connection method	M17 circular connector
-------------------	------------------------

IBS IP CDIO/R 24-12/4/8-SF - I/O module



2730077

<https://www.phoenixcontact.com/us/products/2730077>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
----------------------	------

Mounting

Mounting type	Panel mounting
---------------	----------------

IBS IP CDIO/R 24-12/4/8-SF - I/O module


2730077

<https://www.phoenixcontact.com/us/products/2730077>



Drawings

Dimensional drawing



IBS IP CDIO/R 24-12/4/8-SF - I/O module



2730077

<https://www.phoenixcontact.com/us/products/2730077>

Classifications

UNSPSC

UNSPSC 21.0	32151602
-------------	----------

2730077

<https://www.phoenixcontact.com/us/products/2730077>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com