

IBS PCI RI/I-T - Termination board



2730129

<https://www.phoenixcontact.com/us/products/2730129>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Termination board, with copper connection and external power supply



Product description

The slave controller boards are intelligent PC boards that link the PC to any position in the INTERBUS system. This makes it possible to set up powerful visualization stations which allow access to data in the INTERBUS system and the controller close to the application. Several cards can be installed simultaneously in one PC so that it is possible to visualize or monitor several INTERBUS lines in one single PC. The number of data words that the slave controller boards occupy in the INTERBUS system can be set between one and eighteen. The interface cards provide a freely configurable fast I/O channel for time-critical data and also support the INTERBUS parameter channel (PCP). The parameter channel provides an optional access to larger data blocks.

Your advantages

- Parameterization and diagnostics with Diag+
- INTERBUS parameter channel (PCP) supported
- Access to INTERBUS system data and controller data via visualization stations
- Compatible driver
- Installation of several cards in a PC with monitoring of multiple INTERBUS lines
- External 24 V DC power supply
- Direct integration into OPC-based visualization systems via OPC server

Commercial data

Item number	2730129
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR14
Product key	DREABA
GTIN	4017918974183
Weight per piece (including packing)	226.2 g
Weight per piece (excluding packing)	226.2 g
Customs tariff number	85176200
Country of origin	DE

IBS PCI RI/I-T - Termination board



2730129

<https://www.phoenixcontact.com/us/products/2730129>

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	PC controller board
Type	PC card
Format	Short plug-in card, 1-slot

System properties

Control system	IBM-compatible PCs with PCI slot
Operating system	Windows NT
	Windows 2000
	Windows XP

INTERBUS-Master

Amount of process data	max. 8192 Byte (INTERBUS-Master)
	256 bit (INTERBUS-Slave)
Number of parameter data	4 Byte
Number of devices with parameter channel	max. 126

Function

Function block	Diagnostics
	IO exchange
	PCP
	NV-RAM
	directs I/Os

Functionality

Control system	IBM-compatible PCs with PCI slot
----------------	----------------------------------

System requirements

Configuration tool	Own configurator on CD
Application interface	DDI
	OPC-DA server
Driver	Windows NT
	Windows 2000
	Windows XP

Electrical properties

Transmission medium	Copper
Maximum power dissipation for nominal condition	max. 5 W

IBS PCI RI/I-T - Termination board



2730129

<https://www.phoenixcontact.com/us/products/2730129>

Supply

Supply voltage	3.3 V DC (internal)
	5 V DC (internal)
	24 V DC (external)
Supply voltage range	18 V DC ... 30 V DC
Power supply connection	Via PCI bus or 2-pos. MINI-COMBICON
Typical current consumption	1 A

Input data

Counter:

Number of inputs	0
Input frequency	0 kHz

Output data

Pulse direction

Number of pulse direction outputs	0
Limit frequency	0 kHz

Interfaces

Interrupts	1 IRQ, PNP
------------	------------

INTERBUS remote bus, incoming

Connection method	9-pos. D-SUB pin strip
Transmission speed	500 kbps / 2 Mbps (can be switched)

INTERBUS remote bus, outgoing

Connection method	9-pos. D-SUB socket strip
Transmission speed	500 kbps / 2 Mbps (can be switched)

Host system

Connection method	PCI slot in acc. with PCI specification 2.1 or higher, PCI bus, 32 bits, 33 MHz, 3.3/5 V
-------------------	--

External power supply

Connection method	2-pos. MINI PCB terminal block
-------------------	--------------------------------

Dimensions

Width	134 mm
Height	107 mm
Depth	20 mm

External dimensions

Width / Height / Depth	134 mm / 107 mm / 20 mm
------------------------	-------------------------

Environmental and real-life conditions

IBS PCI RI/I-T - Termination board



2730129

<https://www.phoenixcontact.com/us/products/2730129>

Ambient conditions

Degree of protection	IP20 (Must be installed in a device with IP20)
Ambient temperature (operation)	0 °C ... 55 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	95 % (non-condensing)
Permissible humidity (storage/transport)	95 % (non-condensing)

Mounting

Mounting type	In the host system
---------------	--------------------

2730129

<https://www.phoenixcontact.com/us/products/2730129>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com