

FLS IB M12 DIO 8/8 M12 - Distributed I/O device



2736385

<https://www.phoenixcontact.com/us/products/2736385>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The stand-alone device for INTERBUS has 8 digital inputs and 8 digital outputs each with a load capacity of 500 mA. The M12 connection is established using fast connection technology. The 24 V DC supply is protected against short circuit and overload.

Product description

This device is used for digital signal acquisition and output.

Your advantages

- Flexible power supply concept
- Diagnostic and status indicators
- Short-circuit and overload protection
- SPEEDCON fast locking system
- Consistent connection via M12 connectors

Commercial data

Item number	2736385
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR03
Product key	DRI4A1
GTIN	4017918943257
Weight per piece (including packing)	382.5 g
Weight per piece (excluding packing)	340 g
Customs tariff number	85176200
Country of origin	CN

FLS IB M12 DIO 8/8 M12 - Distributed I/O device




2736385

<https://www.phoenixcontact.com/us/products/2736385>

Technical data

Dimensions

Dimensional drawing	
Width	60 mm
Height	178 mm
Depth	49.3 mm
Drill hole spacing	168 mm

Interfaces

INTERBUS

Connection method	2x M12 connectors, B-coded
Designation connection point	Copper cable
Number of positions	5
Transmission speed	500 kbps

System properties

System limits

Number of local bus devices that can be connected	0
Number of devices with parameter channel	0

Programming data

Length code (hex)	81
ID code (dec.)	3
Length code (dec)	129
Process data channel	8 bit
Input address area	8 bit
Output address area	8 bit
Parameter channel (PCP)	0 bit
Register length (bus)	8 bit

Input data

Digital:

Input name	Digital inputs
Description of the input	IEC 61131-2 type 1
Number of inputs	8
Connection method	M12 connector double occupancy
Connection technology	2-, 3-, 4-conductor

2736385

<https://www.phoenixcontact.com/us/products/2736385>

Input voltage	24 V DC
Input voltage range "0" signal	-30 V DC ... 5 V DC
Input voltage range "1" signal	13 V DC ... 30 V DC
Nominal input voltage U_{IN}	24 V DC
Total sensor current	max. 600 mA
Filter time	3 ms
Protective circuit	Reverse polarity protection

Output data

Digital:

Output name	Digital outputs
Connection method	M12 connector double occupancy
Connection technology	2-, 3-conductor
Number of outputs	8
Protective circuit	Short-circuit protection
Output voltage	24 V DC
Maximum output current per channel	500 mA

Product properties

Product type	I/O component
Product family	Fieldline
Type	Stand-alone
No. of channels	16

Electrical properties

Potentials

Voltage supply U_L	24 V DC
Power supply at U_L	max. 4 A
Current consumption from U_L	typ. 60 mA max. 100 mA
Voltage supply U_S	24 V DC
Power supply at U_S	max. 4 A
Current consumption from U_S	typ. 10 mA (plus sensor current) max. 500 mA
Voltage supply U_{A11}	24 V DC
Power supply at U_{A11}	max. 4 A
Current consumption at U_{A11}	typ. 6 mA (plus actuator current) max. 4 A
Voltage supply U_{A12}	24 V DC
Power supply at U_{A12}	max. 4 A
Current consumption at U_{A12}	typ. 6 mA (plus actuator current) max. 4 A

Supply: Module electronics

FLS IB M12 DIO 8/8 M12 - Distributed I/O device



2736385

<https://www.phoenixcontact.com/us/products/2736385>

Connection method	M12 connector, A-coded
Designation	U _L
Supply voltage	24 V DC
Supply voltage range	18 V DC ... 30 V DC (including ripple)

Electrical isolation/isolation of the voltage ranges

Test voltage: To I/O	500 V AC
----------------------	----------

Connection data

Connection method	M12 connector
-------------------	---------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Degree of protection	IP65/IP67
Air pressure (operation)	80 kPa ... 106 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (storage/transport)	95 %

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	Panel mounting
---------------	----------------

FLS IB M12 DIO 8/8 M12 - Distributed I/O device




2736385

<https://www.phoenixcontact.com/us/products/2736385>


Drawings

Dimensional drawing



Dimensions of the module

Connection diagram




FLS IB M12 DIO 8/8 M12 - Distributed I/O device

2736385

<https://www.phoenixcontact.com/us/products/2736385>

Block diagram



FLS IB M12 DIO 8/8 M12 - Distributed I/O device



2736385

<https://www.phoenixcontact.com/us/products/2736385>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2736385>

INTERBUS CLUB

Approval ID: 426/06.04.04

FLS IB M12 DIO 8/8 M12 - Distributed I/O device



2736385

<https://www.phoenixcontact.com/us/products/2736385>

Classifications

UNSPSC

UNSPSC 21.0	32151602
-------------	----------

2736385

<https://www.phoenixcontact.com/us/products/2736385>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com