

IB IL 24 PWR IN/2-F-D - Inline terminal



2860280

<https://www.phoenixcontact.com/us/products/2860280>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Inline power terminal block, without accessories, 24 V DC, with fuse (Main and segment voltage) and diagnostics



The figure shows version IB IL 24 PWR
IN/F

Your advantages

- Diagnostic and status indicators
- Protection of the segment circuit using an electronic fuse with short-circuit current limitation
- Feed-in or provision of the 24 V segment voltage U_{S}
- Supply of the 24 V main voltage U_{M}

Commercial data

Item number	2860280
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRI121
GTIN	4017918822750
Weight per piece (including packing)	66.9 g
Weight per piece (excluding packing)	52.59 g
Customs tariff number	85389091
Country of origin	DE

Technical data

Product properties

Type	modular
	Inline
Number of plugs	1

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

System properties

Local diagnostics

Error messages via the bus	/O error message when fuse triggered or missing
----------------------------	-------------------------------------------------

Module

ID code (dec.)	190
ID code (hex)	BE
Length code (hex)	C2
Length code (dec)	194
Process data channel	2 bit
Input address area	2 bit
Output address area	0 Byte
Register length	2 bit
Required parameter data	1 Byte

Electrical properties

Test section	5 V supply, incoming remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	5 V supply, outgoing remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	5 V supply, outgoing remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	24 V supply (I/O) / functional ground 500 V AC 50 Hz 1 min
Protective circuit	Polarity protection, surge protection
	Overload protection; Fuse
Fuse	SI 5 x 20 6, 300 AT (in scope of delivery)

Supply

Communications power U_L	7.5 V DC (via voltage jumper)
I/O voltage	24 V DC
I/O voltage range	19.2 V ... 30 V DC (including all tolerances, including ripple)
Residual ripple	$\pm \pm 5$ %
Max. current consumption	4 A
Typical current consumption	30 mA

Potentials: Communications power (U_L)

IB IL 24 PWR IN/2-F-D - Inline terminal

2860280

<https://www.phoenixcontact.com/us/products/2860280>

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 25 mA DC (maximum)

Potentials: Main circuit supply (U_M)

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V ... 30 V (including all tolerances, including ripple)
Power supply	max. 4 A (sum of $U_M + U_S$)

Potentials: Segment circuit supply (U_S)

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 4 A (sum of $U_M + U_S$)

Connection data

Inline connector


Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16

Interfaces

Inline local bus

Connection method	Inline data jumper
-------------------	--------------------

Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm

Material specifications

Color	green
-------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C

IB IL 24 PWR IN/2-F-D - Inline terminal



2860280

<https://www.phoenixcontact.com/us/products/2860280>

Permissible humidity (operation)	75 % ... 85 % (in the range of -25°C ... +55°C, appropriate measures against increased humidity (> 85%) must be taken.)
Permissible humidity (storage/transport)	75 % ... 85 % (Slight temporary condensation may sometimes appear on the housing, e.g. when the terminal block is brought out of a vehicle into an enclosed room.)

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL 24 PWR IN/2-F-D - Inline terminal

2860280

<https://www.phoenixcontact.com/us/products/2860280>

Drawings

Dimensional drawing




IB IL 24 PWR IN/2-F-D - Inline terminal

2860280

<https://www.phoenixcontact.com/us/products/2860280>

Connection diagram




IB IL 24 PWR IN/2-F-D - Inline terminal

2860280

<https://www.phoenixcontact.com/us/products/2860280>



Block diagram



IB IL 24 PWR IN/2-F-D - Inline terminal



2860280

<https://www.phoenixcontact.com/us/products/2860280>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com