

IB IL 24 FLM-PAC - Communication module




2736903

<https://www.phoenixcontact.com/us/products/2736903>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Inline, Branch terminal, for extending the Inline local bus, transmission speed in the local bus: 500 kbps / 2 Mbps, degree of protection: IP20, including Inline connector and labeling field



Your advantages


- Connection of Fieldline Modular M8 to Fieldline Modular M12
- Connection of Fieldline Modular M8 or M12 to Inline Modular

Commercial data

Item number	2736903
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI152
GTIN	4046356079204
Weight per piece (including packing)	83 g
Weight per piece (excluding packing)	43 g
Customs tariff number	85389099
Country of origin	DE

Technical data

Dimensions

Dimensional drawing	
Width	12.2 mm
Height	136.8 mm
Depth	71.5 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Utilization restriction

CCcex note	Use in potentially explosive areas is not permitted in China.
------------	---

Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

Interfaces

Inline local bus

Number of interfaces	1 (incoming local bus)
Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps (Can be used in Inline stations with these transmission speeds)

Inline local bus

No. of channels	outgoing local bus
Connection method	Inline shield connector
Note on the connection method	Standard INTERBUS cable
Transmission speed	500 kbps / 2 Mbps

System properties

Programming data (LocalbusSlave)

ID code (dec.)	none
----------------	------

2736903

<https://www.phoenixcontact.com/us/products/2736903>

Input address area	0 Byte
Output address area	0 Byte
Parameter channel (PCP)	0 Byte
Register length (bus)	0 Byte

Fieldbus data telegram

Required parameter data	0 Byte
Required configuration data	0 Byte

Product properties

Product type	I/O component
Product family	Inline
Type	modular
Installation location	Control cabinet
Scope of supply	including Inline connector and labeling field
Special properties	for extending the Inline local bus

Electrical properties

Maximum power dissipation for nominal condition	0.85 W
---	--------

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	110 mA

Potentials

Supply voltage	24 V DC
Current draw	max. 6 A (Fieldline Modular M8 local bus, with both-side supply; maximum 3 A for go and return line each)
	max. 55 mA (internal)

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 106 kPa (up to 2000 m above sea level)

IB IL 24 FLM-PAC - Communication module



2736903

<https://www.phoenixcontact.com/us/products/2736903>

Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	75 % (On average, 85 % occasionally)
Permissible humidity (storage/transport)	75 % (On average, 85 % occasionally)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL 24 FLM-PAC - Communication module



2736903


<https://www.phoenixcontact.com/us/products/2736903>

Drawings

Dimensional drawing



Connection diagram



IB IL 24 FLM-PAC - Communication module



2736903

<https://www.phoenixcontact.com/us/products/2736903>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2736903>



cULus Recognized

Approval ID: E140324



cULus Listed

Approval ID: E199827

IB IL 24 FLM-PAC - Communication module



2736903

<https://www.phoenixcontact.com/us/products/2736903>

Classifications

ECLASS

ECLASS-13.0	27242608
ECLASS-15.0	27242608

ETIM

ETIM 10.0	EC001604
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

2736903

<https://www.phoenixcontact.com/us/products/2736903>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)
SCIP	d40353be-44b3-4e43-bd3b-e984f74d5bf8

EF3.1 Climate Change

CO2e kg	1.709 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com