

IB IL RS 232-PAC - Communication module



2861357

<https://www.phoenixcontact.com/us/products/2861357>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Communication module, Serial data transmission; interface: RS-232: 1; Transmission speed: 110 bps ... 38400 bps; transmission speed in the local bus: 500 kbps; degree of protection: IP20; Communication via PCP; Scope of supply: including Inline connectors and marking fields

Product description

The terminal is designed for use within an Inline station. The terminal can be used to operate standard I/O devices with serial interfaces on a bus system.

Your advantages


- One serial RS-232 input and output channel
- Various protocols supported
- Transmission speed can be set up to 38400 bps
- Number of data bits, stop bits and parity can be set
- 4 kbyte receive buffer and 1 kbyte transmit buffer
- Parameterization and data exchange via PCP

Commercial data

Item number	2861357
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI151
GTIN	4017918894290
Weight per piece (including packing)	150.7 g
Weight per piece (excluding packing)	135 g
Customs tariff number	85389091
Country of origin	DE

Technical data

Dimensions

Dimensional drawing	
Width	24.4 mm
Height	136.8 mm
Depth	71.5 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

Interfaces

Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps

RS-232

Number of interfaces	1
Connection method	Spring-cage connection
Transmission speed	110 bps ... 38400 bps (can be parameterized)
Transmission physics	Copper
Data bits	7 or 8
Stop bits	1 or 2
Input buffer	4 kByte
Output buffer	1 kByte

System properties

Programming data (LocalbusSlave)

Length code (hex)	01
ID code (dec.)	220
Length code (dec)	01
Process data channel	16 bit
Input address area	2 Byte

Output address area	2 Byte
Parameter channel (PCP)	4 Byte
Register length (bus)	6 Byte

Fieldbus data telegram

Required parameter data	27 Byte
Required configuration data	5 Byte

Product properties

Product type	I/O component
Product family	Inline
Type	modular
Scope of supply	including Inline connectors and marking fields
Special properties	Communication via PCP

Electrical properties

Maximum power dissipation for nominal condition	1.7 W
---	-------

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 225 mA (all connections of the serial interface are short-circuited) typ. 155 mA

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

IB IL RS 232-PAC - Communication module



2861357

<https://www.phoenixcontact.com/us/products/2861357>

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL RS 232-PAC - Communication module



2861357


<https://www.phoenixcontact.com/us/products/2861357>

Drawings


Dimensional drawing



Connection diagram



Block diagram



IB IL RS 232-PAC - Communication module



2861357

<https://www.phoenixcontact.com/us/products/2861357>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2861357>



DNV GL

Approval ID: TAA00001KV



LR

Approval ID: LR23398855TA



BV

Approval ID: 21595/C1 BV



RINA

Approval ID: ELE121121XG

ABS

Approval ID: 22-2226444-PDA



cULus Recognized

Approval ID: E140324

IB IL RS 232-PAC - Communication module



2861357

<https://www.phoenixcontact.com/us/products/2861357>

Classifications

ECLASS

ECLASS-13.0	27242608
ECLASS-15.0	27242608

ETIM

ETIM 10.0	EC001604
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

2861357

<https://www.phoenixcontact.com/us/products/2861357>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0c8d3621-4785-4d01-83d9-80cfdd748a5d

EF3.1 Climate Change

CO2e kg	8.783 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com