

# IB IL 24 TC-PAC - Analog module



2861360

<https://www.phoenixcontact.com/us/products/2861360>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Inline thermistor terminal, complete with accessories (connector and marking field), 2-conductor connection technology



## Your advantages

- Connection for a thermistor
- Integrated switching output
- Maximum permissible load current: 500 mA
- Diagnostic and status indicators

## Commercial data

Item number	2861360
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI143
GTIN	4017918894306
Weight per piece (including packing)	83 g
Weight per piece (excluding packing)	50 g
Customs tariff number	85389099
Country of origin	DE


# IB IL 24 TC-PAC - Analog module

2861360

<https://www.phoenixcontact.com/us/products/2861360>

## Technical data

### Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm

### Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

### Interfaces

Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps
Transmission physics	Copper

### System properties

Programming data (LocalbusSlave)

Length code (hex)	41
ID code (dec.)	190
Length code (dec)	65
Process data channel	4 bit
Input address area	4 bit
Output address area	0 Byte
Parameter channel (PCP)	0 Byte
Register length (bus)	4 bit

Fieldbus data telegram

Required parameter data	1 Byte
Required configuration data	4 Byte

### Input data

# IB IL 24 TC-PAC - Analog module



2861360

<https://www.phoenixcontact.com/us/products/2861360>

## Analog:

Input name	Resistance sensor
Description of the input	Input for PTC thermistor
Number of inputs	1
Connection method	Spring-cage connection
Connection technology	2-conductor
Sensor types (RTD) that can be used	PTC thermistor according to DIN 44081 or DIN 44082
Input filter time	typ. 10 ms
Nominal value of the current sources	max. 1.2 mA (for open-circuit voltage of < 8 V DC)
Linear resistance measuring range	2.7 k $\Omega$ ... 3.5 k $\Omega$ (Shutdown range, total resistance) 50 $\Omega$ ... 2.25 k $\Omega$ (Operating range, total resistance)

## Output data

### Analog:

Connection method	Spring-cage connection
Connection technology	2-conductor
Number of outputs	1
Protective circuit	short-circuit and overload proof
Current output signal	500 mA (per output)
Voltage output signal	24 V DC ( $U_S - 1$ V)
Load/output load voltage output	< 2.7 k $\Omega$ (Total resistance for output signal HIGH)

## Product properties

Product type	I/O component
Product family	Inline
Type	modular
Installation location	Control cabinet

## Electrical properties

Maximum power dissipation for nominal condition	0.6 W
---	-------

### Potentials: Communications power ( $U_L$ )

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 60 mA

### Potentials: Segment circuit supply ( $U_S$ )

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 500 mA

### Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min

# IB IL 24 TC-PAC - Analog module



2861360

<https://www.phoenixcontact.com/us/products/2861360>

Test voltage: 7.5 V supply (bus logics)/24 V analog supply (analog I/O)	500 V AC, 50 Hz, 1 min
Test voltage: 24 V analog supply (analog I/O)/functional ground	500 V AC, 50 Hz, 1 min
Test voltage: Thermistor / all other areas	1200 V AC, 50 Hz, 1 min

## Connection data

### Connection technology

Connection name	Inline connector
-----------------	------------------

### Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 106 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	-25 % ... 55 % (75% average, 85% seldom)
Permissible humidity (storage/transport)	-25 % ... 85 %

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IB IL 24 TC-PAC - Analog module



2861360

<https://www.phoenixcontact.com/us/products/2861360>

## Drawings

Dimensional drawing




# IB IL 24 TC-PAC - Analog module

2861360

<https://www.phoenixcontact.com/us/products/2861360>



Connection diagram



# IB IL 24 TC-PAC - Analog module



2861360

<https://www.phoenixcontact.com/us/products/2861360>

## Classifications

### ECLASS

ECLASS-13.0	27242601
ECLASS-15.0	27242601

### ETIM

ETIM 10.0	EC001596
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# IB IL 24 TC-PAC - Analog module



2861360

<https://www.phoenixcontact.com/us/products/2861360>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	fd9be18a-16a8-4c03-b96c-8d8294d6c25b

### EF3.1 Climate Change

CO2e kg	2.516 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)