

IB IL 400 SAFE 2 - Inline terminal



2740795

<https://www.phoenixcontact.com/us/products/2740795>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Inline safety terminal, three N/O contacts, one N/C contact, 200 V AC - 600 V AC



Product description

The IB IL 400 SAFE 2 safety terminal in conjunction with the IB IL 24 SAFE 1 safety terminal is designed for use within an Inline station. The terminal acts as a contact expansion for IB IL 24 SAFE 1 and switches off the 400 V three-phase power supply of the downstream power-level terminals used for switching asynchronous motors. The wiring is such that the terminal can be used in direct connection with the IB IL 24 SAFE 1 in applications in all safety categories, including category 4.

Commercial data

Item number	2740795
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN03
Product key	DNA45Z
GTIN	4017918193805
Weight per piece (including packing)	841.4 g
Weight per piece (excluding packing)	841.4 g
Customs tariff number	85369010
Country of origin	DE


IB IL 400 SAFE 2 - Inline terminal

2740795

<https://www.phoenixcontact.com/us/products/2740795>

Technical data

Dimensions

Dimensional drawing	
Width	63 mm
Height	224 mm
Depth	109 mm

Material specifications

Color	green
-------	-------

Interfaces

Inline local bus

Connection method	Inline data jumper
-------------------	--------------------

Output data

Digital:

Output name	Relay output
Number of outputs	4
Protective circuit	Short-circuit and overload protection; Fuse type 2, 20 A gG (gl)
Output voltage range	< 187 V AC ... 480 V AC +0 % (Operating voltage (line voltage))
Nominal load, ohmic	max. 5500 W
Signal delay	typ. 45 ms (Off delay)

Relay

Contact switching type	3 N/O contacts, 1 N/C contact (feedback)
Contact connection type	Positively driven
Switching voltage	200 V AC (up to 600 V AC)
Switching current	12 A (at 400 V AC)
Switching power	5500 VA
Min. switching current	100 mA
Switching frequency	max. 30 (per minute)
Release time	< 20 ms

Product properties

Product type	I/O component
Product family	Inline

IB IL 400 SAFE 2 - Inline terminal



2740795

<https://www.phoenixcontact.com/us/products/2740795>

Type	modular
Mounting position	Horizontal DIN rail
No. of channels	1

Electrical properties

Potentials: Segment circuit supply (U_S)

Supply voltage	24 V DC (nominal value)
Current draw	max. 270 mA

Supply: Module electronics

Connection method	Through the potential jumper
Supply voltage	24 V DC (Removal from the segment circuit)
Supply voltage range	20.4 V DC ... 27.6 V DC (including ripple)
Supply current	max. 270 mA (From U_S)
Current consumption	max. 270 mA

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 45 °C (Deviation from the Inline specifications)
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 106 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	75 % ... 85 % (75% average, 85% seldom)
Permissible humidity (storage/transport)	75 % ... 85 % (75% average, 85% seldom)

Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	1g, 2 h in each direction
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	5g, 11 ms period, half-sine shock pulse

Standards and regulations

Protection class	I (IEC 61140, EN 61140, VDE 0140-1)
------------------	-------------------------------------

Mounting

IB IL 400 SAFE 2 - Inline terminal



2740795

<https://www.phoenixcontact.com/us/products/2740795>

Mounting type	DIN rail mounting
Mounting position	Horizontal DIN rail

IB IL 400 SAFE 2 - Inline terminal


2740795

<https://www.phoenixcontact.com/us/products/2740795>




Drawings

Dimensional drawing



Connection diagram



IB IL 400 SAFE 2 - Inline terminal



2740795

<https://www.phoenixcontact.com/us/products/2740795>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com