

IB IL 24 AI 2/SF-230 - Inline terminal

2740818

<https://www.phoenixcontact.com/us/products/2740818>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Inline analog input terminal, without accessories, 2 inputs, 0 - 20 mA, 4 - 20 mA, ± 20 mA, 0 - 10 V, ± 10 V, 3 dB cut-off frequency at 230 Hz, 2-conductor connection technology



The figure shows version IB IL AI 2/SF

Product description

The terminal is designed for use within an Inline station. It is used to acquire analog voltage and current signals.

Commercial data

Item number	2740818
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRI141
GTIN	4017918574789
Weight per piece (including packing)	67.2 g
Weight per piece (excluding packing)	52.89 g
Customs tariff number	85389091
Country of origin	DE

2740818

<https://www.phoenixcontact.com/us/products/2740818>

Technical data

Product properties

Type	modular
	Inline

System properties

Programming data

Length code (hex)	02
ID code (dec.)	127
Length code (dec)	02
Input address area	4 Byte
Output address area	4 Byte
Parameter channel (PCP)	0 Byte
Register length (bus)	32 bit

Fieldbus data telegram

Required parameter data	6 Byte
-------------------------	--------

Electrical properties

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 60 mA typ. 45 mA

Potentials: Supply of analog modules (U_{ANA})

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 18 mA typ. 13 mA

Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logic), 24 V supply U_{ANA} / I/O	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logic), 24 V supply U_{ANA} / functional ground	500 V AC, 50 Hz, 1 min
Test voltage: I/O/functional ground	500 V AC, 50 Hz, 1 min

Input data

Analog: General

Input name	Analog inputs
------------	---------------

IB IL 24 AI 2/SF-230 - Inline terminal



2740818

<https://www.phoenixcontact.com/us/products/2740818>

Number of inputs	max. 2 (single ended)
A/D conversion time	120 µs (per channel)
Connection technology	2-conductor (shielded)
Current input signal	0 mA ... 20 mA 4 mA ... 20 mA -20 mA ... 20 mA
Voltage input signal	0 V ... 10 V -10 V ... 10 V
Input resistance of voltage input	< 220 kΩ
A/D converter resolution	16 bit
Data formats	IB IL, IB ST, IB RT, standardized representation
Limit frequency (3 dB)	40 Hz 230 Hz
Measured value representation	16 bits (15 bits + sign bit)

Analog: Voltage inputs

Number of inputs	2 (Single-ended voltage inputs)
Voltage input signal	0 V ... 10 V -10 V ... 10 V
Input resistance of voltage input	220 kΩ
A/D converter resolution	15 bit
Measuring principle	Successive approximation
Measured value resolution	16 bits (15 bits + sign bit)
Measured value representation	16 bit two's complement

Analog: Current inputs

Number of inputs	2 (single-ended current inputs)
Current input signal	0 mA ... 40 mA 4 mA ... 20 mA -20 mA ... 20 mA
Input resistance current input	50 Ω 0.02 %
Limit frequency (3 dB)	15 Hz (40 Hz)

Connection data

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16

Interfaces

Inline local bus

No. of channels	2
Connection method	Inline data jumper

IB IL 24 AI 2/SF-230 - Inline terminal



2740818

<https://www.phoenixcontact.com/us/products/2740818>

Transmission speed	500 kbps
Transmission physics	Copper

Dimensions

Dimensional drawing	
Width	12.2 mm
Height	136.8 mm
Depth	71.5 mm

Material specifications

Color	green
-------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL 24 AI 2/SF-230 - Inline terminal



2740818


<https://www.phoenixcontact.com/us/products/2740818>

Drawings

Dimensional drawing



Connection diagram



IB IL 24 AI 2/SF-230 - Inline terminal

2740818

<https://www.phoenixcontact.com/us/products/2740818>



Block diagram



IB IL 24 AI 2/SF-230 - Inline terminal



2740818

<https://www.phoenixcontact.com/us/products/2740818>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com