

# IB IL 24 EDO 2-PAC - Inline terminal

2861616

<https://www.phoenixcontact.com/us/products/2861616>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline digital output terminal, complete with accessories (connector and marking field), 2 outputs, 24 V DC, 500 mA, 2-, 3-, 4-conductor connection technology, extended diagnostics, parameterizable outputs

## Your advantages

- Wire-break detection
- Short-circuit and overload-protected outputs
- Nominal current per output: 500 mA
- Connection of actuators in 2-, 3-, and 4-conductor technology
- Connection for 2 digital actuators
- Total current of the terminal: 1 A

## Commercial data

Item number	2861616
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR01
Product key	DRI132
GTIN	4017918894467
Weight per piece (including packing)	81.8 g
Weight per piece (excluding packing)	41 g
Customs tariff number	85389091
Country of origin	DE

# IB IL 24 EDO 2-PAC - Inline terminal

2861616

<https://www.phoenixcontact.com/us/products/2861616>

## Technical data

### Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Material specifications

Color	green
-------	-------

### Interfaces

#### Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps

### System properties

#### Module

ID code (dec.)	191
ID code (hex)	BF
Length code (hex)	41
Length code (dec)	65
Process data channel	4 bit
Input address area	4 bit
Output address area	4 bit
Register length	4 bit
Required parameter data	3 Byte
Required configuration data	5 Byte

### Output data

# IB IL 24 EDO 2-PAC - Inline terminal



2861616

<https://www.phoenixcontact.com/us/products/2861616>

## Digital:

Output name	Digital outputs
Output description	Extended diagnostics, parameterizable outputs
Connection method	Spring-cage connection
Connection technology	2-, 3-, 4-conductor
Number of outputs	2
Protective circuit	Overload protection, short-circuit protection of outputs
Output voltage	24 V DC ( $U_S - 1$ V)
Maximum output current per channel	500 mA
Maximum output current per module	1 A
Nominal output voltage	24 V DC (voltage difference at $I_{nom} \leq 1$ V)
Nominal load, inductive	12 W
Nominal load, lamp	12 W
Nominal load, ohmic	12 VA
Behavior with overload	Auto restart
Behavior with inductive overload	Output can be destroyed
Behavior at voltage switch-off	The output follows the power supply without delay

## Product properties

Product type	I/O component
Product family	Inline
Type	modular Inline
No. of channels	2
Diagnostics messages	Short-circuit or overload of the digital outputs Error message in the diagnostic code (bus) and display (2 Hz) via the LED (D) on the module

## Electrical properties

### Potentials: Communications power ( $U_L$ )

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 40 mA

### Potentials: Main circuit supply ( $U_M$ )

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)

### Potentials: Segment circuit supply ( $U_S$ )

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 1 A

### Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
---	------------------------

# IB IL 24 EDO 2-PAC - Inline terminal



2861616

<https://www.phoenixcontact.com/us/products/2861616>

Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logics)/24 V supply (I/O)	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply (I/O) / functional ground	500 V AC, 50 Hz, 1 min

## Connection data

### Connection technology

Connection name	Inline connector
-----------------	------------------

### Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IB IL 24 EDO 2-PAC - Inline terminal

2861616


<https://www.phoenixcontact.com/us/products/2861616>

## Drawings

Dimensional drawing



Connection diagram




# IB IL 24 EDO 2-PAC - Inline terminal

2861616

<https://www.phoenixcontact.com/us/products/2861616>



Block diagram



# IB IL 24 EDO 2-PAC - Inline terminal



2861616

<https://www.phoenixcontact.com/us/products/2861616>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)