

# IB IL 24 EDI 2-PAC - Inline terminal

2861629

<https://www.phoenixcontact.com/us/products/2861629>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline digital input terminal, complete with accessories (connector and marking field), 2 inputs, 24 V DC, 2-, 3-, 4-conductor connection technology, extended diagnostics, short-circuit-proof initiator supply

## Commercial data

Item number	2861629
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRI131
GTIN	4017918894474
Weight per piece (including packing)	76.9 g
Weight per piece (excluding packing)	62.59 g
Customs tariff number	85389091
Country of origin	DE

# IB IL 24 EDI 2-PAC - Inline terminal



2861629

<https://www.phoenixcontact.com/us/products/2861629>

## Technical data

### Product properties

Type	modular
No. of channels	2

### System properties

#### Programming data

Length code (hex)	C2
ID code (dec.)	190
Length code (dec)	194
Process data channel	2 bit
Input address area	2 bit
Output address area	0 Byte
Parameter channel (PCP)	0 Byte
Register length (bus)	2 bit

#### Fieldbus data telegram

Required parameter data	1 Byte
Required configuration data	4 Byte

### Electrical properties

#### Potentials: Communications power ( $U_L$ )

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 31 mA

#### Potentials: Segment circuit supply ( $U_S$ )

Supply voltage	24 V DC (nominal value)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 0.25 A

#### Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logics)/24 V supply (I/O)	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply (I/O) / functional ground	500 V AC, 50 Hz, 1 min

### Input data

#### Digital:

Input name	Digital inputs
Description of the input	IEC 61131-2 type 1
Number of inputs	2

# IB IL 24 EDI 2-PAC - Inline terminal

2861629

<https://www.phoenixcontact.com/us/products/2861629>

Connection method	Spring-cage connection
Connection technology	4-conductor
Input voltage	24 V DC
Input voltage range "0" signal	-3 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Typical response time	< 1 ms

## Connection data

### Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16

## Interfaces

### Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps (automatic recognition)

## Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)

## Standards and regulations

# IB IL 24 EDI 2-PAC - Inline terminal



2861629

<https://www.phoenixcontact.com/us/products/2861629>

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IB IL 24 EDI 2-PAC - Inline terminal



2861629


<https://www.phoenixcontact.com/us/products/2861629>

## Drawings

Dimensional drawing



Connection diagram



# IB IL 24 EDI 2-PAC - Inline terminal



2861629

<https://www.phoenixcontact.com/us/products/2861629>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)