

IB IL TEMPCON UTH-PAC - Inline function terminal



2861807

<https://www.phoenixcontact.com/us/products/2861807>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline temperature controller, complete with accessories (connector and marking field), 8 inputs for thermocouples, 8 outputs, 24 V DC, 2-conductor connection technology

Your advantages

- 8 analog inputs for thermocouples
- 8 outputs, 24 V DC, 70 mA
- Can be configured as a 2-step controller, 3-step controller, motor step controller or signaling device (threshold value switch)
- Self-tuning
- Heating current and closed-loop control circuit monitoring
- Configuration via engineering tool (configuration software)

Commercial data


Item number	2861807
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR01
Product key	DRI191
GTIN	4017918951030
Weight per piece (including packing)	222.6 g
Weight per piece (excluding packing)	122 g
Customs tariff number	85389091
Country of origin	DE

2861807

<https://www.phoenixcontact.com/us/products/2861807>

Technical data

Dimensions

Dimensional drawing	
Width	48.8 mm
Height	119.8 mm
Depth	71.5 mm

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Interfaces

Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps

Configuration interface

Connection method	V.24
-------------------	------

System properties

Module

ID code (dec.)	191
ID code (hex)	BF
Length code (hex)	02
Length code (dec)	02
Process data channel	32 bit
Input address area	4 Byte
Output address area	4 Byte
Register length	32 bit
Required parameter data	1 Byte
Required configuration data	5 Byte

Output data

Output voltage	24 V DC
Output current	70 mA

2861807

<https://www.phoenixcontact.com/us/products/2861807>

Product properties

Product type	I/O component
Product family	Inline
Type	modular
No. of channels	8
Number of plugs	4

Electrical properties

Test section	5 V supply, incoming remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	5 V supply, outgoing remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	7.5 V supply (bus logics)/24 V supply (I/O) 500 V AC 50 Hz 1 min
	24 V supply (I/O) / functional ground 500 V AC 50 Hz 1 min
	Analog inputs/bus logics 500 V AC 50 Hz 1 min
	Analog inputs / 24 V supply (I/O) 500 V AC 50 Hz 1 min
	Analog inputs/functional ground 500 V AC 50 Hz 1 min

Supply

Supply voltage	24 V DC
Communications power U_L	7.5 V DC
Max. current consumption	4 A
Typical current consumption	250 mA

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
----------------------	------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL TEMPCON UTH-PAC - Inline function terminal



2861807


<https://www.phoenixcontact.com/us/products/2861807>

Drawings

Dimensional drawing



Connection diagram



2861807

<https://www.phoenixcontact.com/us/products/2861807>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com