

IBS ST ZF 24 BK LB-T - Bus coupler

2750772

<https://www.phoenixcontact.com/us/products/2750772>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS-ST bus terminal module, 24 V DC, 9-pos., D-SUB with an additional local bus branch, 15-pos. D-SUB, IP20 protection, consisting of: Terminal part with spring-cage connection and module electronics

The figure shows version IBS ST
24 BK RB-T

Product description

INTERBUS ST bus terminal modules with additional interfaces (Bus)

In addition to configuring a modular input/output station with ST modules, the bus terminal modules with additional INTERBUS interfaces provide the option of connecting further INTERBUS network devices.

The IBS ST 24 BK LB-T module is equipped with an additional local bus interface with a 15-pos. D-SUB connector. The flat pack design input/output modules from PHOENIX CONTACT, for example, and frequency inverters with local bus interfaces can be connected to this interface. An additional remote bus connection is provided by the IBS ST 24 RB-T. All devices with an INTERBUS remote bus interface can be connected in this remote bus branch.

The input/output bus terminal modules with additional fiber optic interfaces are available for integrating INTERBUS compatible devices into an INTERBUS fiber optic network.

All INTERBUS bus terminal modules make it possible to individually enable/disable the additional bus interfaces. To some extent, they perform the role of two bus terminal modules in the INTERBUS system and are also treated as such in the address lists and configuring software (CMD).

Note: When configuring buses branching off from the bus terminal modules, please observe the topology supported by INTERBUS controller boards.

Commercial data

Item number	2750772
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR03
Product key	DRI311
GTIN	4017918132101
Weight per piece (including packing)	516.3 g
Weight per piece (excluding packing)	447.3 g
Customs tariff number	85389091
Country of origin	DE


IBS ST ZF 24 BK LB-T - Bus coupler

2750772

<https://www.phoenixcontact.com/us/products/2750772>

Technical data

Dimensions

Dimensional drawing	
Width	81 mm
Height	117 mm
Depth	116 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Interfaces

INTERBUS

Connection method	9-pos. D-SUB plug/socket
Designation connection point	Incoming/Outgoing Remote Bus
Number of positions	9

ST local bus

Connection method	ST local bus connector
-------------------	------------------------

INTERBUS

Connection method	15-pos. D-SUB sockets
Number of positions	15

Fieldbus: Local bus gateway

Max. number of local bus devices	max. 8
----------------------------------	--------

Product properties

Product type	I/O component
Product family	Smart Terminal ST
Type	modular
Mounting position	Horizontal DIN rail

Electrical properties

Supply: Module electronics

Supply voltage	24 V DC
Supply voltage range	20 V DC ... 30 V DC (including ripple)

IBS ST ZF 24 BK LB-T - Bus coupler



2750772

<https://www.phoenixcontact.com/us/products/2750772>

Current consumption	typ. 150 mA (without ST module expansions)
	typ. 650 mA (For maximum number of I/O modules on the ST local bus)
Ripple	3.6 V _{pp} within the allowable voltage range

Electrical isolation/isolation of the voltage ranges

Test voltage: Incoming remote bus / Outgoing remote bus	500 V AC, 50 Hz, 1 min
Test voltage: Power supply voltage / ST local bus	500 V AC, 50 Hz, 1 min
Test voltage: Incoming remote bus/ST interface	500 V AC, 50 Hz
Test voltage: Incoming remote bus/local bus branch	500 V AC, 50 Hz, 1 min

Connection data

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	86 kPa ... 108 kPa (up to 1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	30 % ... 75 % (non-condensing)
Permissible humidity (storage/transport)	30 % ... 95 % (non-condensing)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
Mounting position	Horizontal DIN rail


IBS ST ZF 24 BK LB-T - Bus coupler

2750772


<https://www.phoenixcontact.com/us/products/2750772>

Drawings

Dimensional drawing



Connection diagram



IBS ST ZF 24 BK LB-T - Bus coupler

2750772

<https://www.phoenixcontact.com/us/products/2750772>



Classifications

ECLASS

ECLASS-13.0	27242608
ECLASS-15.0	27242608

IBS ST ZF 24 BK LB-T - Bus coupler

2750772

<https://www.phoenixcontact.com/us/products/2750772>



Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com