


# IB IL PD GND-PAC - Potential distributors



2862990

<https://www.phoenixcontact.com/us/products/2862990>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline terminal for power distribution (GND), complete with accessories, (connector and labeling field) connections for GND

## Product description

The terminal is designed for use within an Inline station. The terminal has eight GND connections. They therefore enable connection to the station-internal GND of sensors and actuators, which are connected to the IB IL 24 DI.../HD-PAC or IB IL 24 DO.../HD-PAC terminal via 1-conductor technology. They therefore enable connection to the station-internal GND of actuators, which are connected to the IB IL 24 DO 32/HD terminal via 1-conductor technology.

## Your advantages

- Connections for GND

## Commercial data

Item number	2862990
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI124
GTIN	4017918910099
Weight per piece (including packing)	64.74 g
Weight per piece (excluding packing)	44 g
Customs tariff number	85389099
Country of origin	DE

2862990

<https://www.phoenixcontact.com/us/products/2862990>

## Technical data

### Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm

### Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

### Interfaces

Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps

### System properties

Programming data (LocalbusSlave)

ID code (dec.)	none
Register length (bus)	0 bit

Fieldbus data telegram

Required parameter data	0 Byte
Required configuration data	0 Byte

### Product properties

Product type	I/O component
Product family	Inline
Type	modular
Installation location	Control cabinet

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

2862990

<https://www.phoenixcontact.com/us/products/2862990>

## Electrical properties

Maximum power dissipation for nominal condition	0 W
Test section	24 V supply (I/O) / functional ground 500 V AC 50 Hz 1 min

### Supply

I/O voltage	GND
Max. current consumption	8 A

## Connection data

### Connection technology

Connection name	Inline connector
-----------------	------------------

### Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	75 % ... 85 %
Permissible humidity (storage/transport)	75 % ... 85 %

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IB IL PD GND-PAC - Potential distributors



2862990

<https://www.phoenixcontact.com/us/products/2862990>


## Drawings

Dimensional drawing



Connection diagram

**E.g., for single-wire connection with  
IB IL 24 DO 32/HD**



# IB IL PD GND-PAC - Potential distributors



2862990

<https://www.phoenixcontact.com/us/products/2862990>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2862990>



**LR**

Approval ID: LR23398855TA



**BV**

Approval ID: 20989\_C1 BV

**ABS**

Approval ID: 22-2226444-PDA

**DNV**

Approval ID: TAA00002CU

# IB IL PD GND-PAC - Potential distributors



2862990

<https://www.phoenixcontact.com/us/products/2862990>

## Classifications

### ECLASS

ECLASS-13.0	27242692
ECLASS-15.0	27242692

### ETIM

ETIM 10.0	EC002584
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# IB IL PD GND-PAC - Potential distributors



2862990

<https://www.phoenixcontact.com/us/products/2862990>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.861 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)