

# UEGH 25 - Electronics housing

2757115

<https://www.phoenixcontact.com/us/products/2757115>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronic housing, double-level, fully equipped with 6 screw connections per side for one printed circuit board

The figure shows version UEGH  
22,5

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2757115       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AC11          |
| Product key                          | ACHCCD        |
| GTIN                                 | 4017918108021 |
| Weight per piece (including packing) | 78.9 g        |
| Weight per piece (excluding packing) | 78.9 g        |
| Customs tariff number                | 85369010      |
| Country of origin                    | DE            |

2757115

<https://www.phoenixcontact.com/us/products/2757115>

## Technical data

### Product properties

|                              |  |
|------------------------------|--|
| Product type                 | Complete housing                             |
| Housing type                 | Complete housing                             |
| Housing series               | UEGH   |
| Product family               | UEGH   |
| Type                         | Connection system integrated, housing closed |
| Number of positions          | 12   |
| Pitch                        | 5 mm   |
| Number of rows               | 2  |
| Ventilation openings present | no   |
| Pin layout                   | Linear pinning                               |

### Electrical properties

|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 500 V |
| Nominal current $I_N$ | 10 A  |

### Connection data

|                   |                  |
|-------------------|------------------|
| Connection method | Screw connection |
|-------------------|------------------|

### Dimensions

|                  |          |
|------------------|----------|
| Width            | 25 mm    |
| Installed height | 106.7 mm |
| Height NS 35/7,5 | 106.7 mm |
| Depth            | 79 mm    |
| Length           | 79 mm    |
| Pitch            | 5 mm     |

### Material specifications

|  |                  |
|--|------------------|
| Color (Housing)                        | green (RAL 6021) |
| Material Housing                       | PA               |
| Flammability rating according to UL 94 | V0               |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 105 °C |
|---------------------------------|-------------------|

### Mounting

|               |                |
|---------------|----------------|
| Mounting type | Soldering      |
| Pin layout    | Linear pinning |

# UEGH 25 - Electronics housing


2757115

<https://www.phoenixcontact.com/us/products/2757115>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2757115>

|  <b>cULus Recognized</b><br>Approval ID: E60425-19770427 |  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|---|--|-----------------------|-----------------------|-------------------|-----------------------------|
| B   |  | 300 V                 | 10 A                  | 30 - 12           | -                           |
| D   |  | 300 V                 | 10 A                  | 30 - 12           | -                           |

# UEGH 25 - Electronics housing

2757115

<https://www.phoenixcontact.com/us/products/2757115>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190501 |
| ECLASS-15.0 | 27190501 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001031 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# UEGH 25 - Electronics housing



2757115

<https://www.phoenixcontact.com/us/products/2757115>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.516 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)