

PSM-EG-RS232/RS485-P/2D - Interface converter



2761392

<https://www.phoenixcontact.com/us/products/2761392>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Interface converter, for converting RS-232 to RS-485 2-wire, with electrical isolation, DIN-rail mountable

The figure shows a variant of the V.24 (RS-232)/RS-422 converter

Commercial data

Item number	2761392
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN05
Product key	DNC112
GTIN	4017918064686
Weight per piece (including packing)	293.6 g
Weight per piece (excluding packing)	293.6 g
Customs tariff number	85176200
Country of origin	DE

Technical data

Product properties

Product type	Interface converter
--------------	---------------------

Electrical properties

Electrical isolation	VCC // V.24 (RS-232) // RS-485
Maximum power dissipation for nominal condition	3.12 W
Test voltage data interface/power supply	2.5 kV
	2.5 kV AC
Test voltage data interfaces	2.5 kV AC

Supply

Nominal supply voltage	24 V DC \pm 20 %
Typical current consumption	130 mA (24 V DC)

Connection data

Supply

Tightening torque	0.56 Nm ... 0.79 Nm
-------------------	---------------------

Interfaces

Bit distortion	\leq 5 %
Bit delay	\leq 3 μ s
Signal	Modbus

Data

Transmission length	15 m (twisted pair)
Conductor cross-section flexible max.	2.5 mm ²
Conductor cross-section flexible min.	0.2 mm ²
Conductor cross-section AWG max.	14
Conductor cross-section AWG min.	24

Dimensions

Width	45 mm
Height	75 mm
Depth	110 mm

Material specifications

Color (Housing)	green (RAL 6021)
Material (Housing)	ABS

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 50 °C
---------------------------------	----------------

PSM-EG-RS232/RS485-P/2D - Interface converter



2761392

<https://www.phoenixcontact.com/us/products/2761392>

Approvals

UL, USA/Canada

Identification

UL 508 Recognized

EMC data

Electromagnetic compatibility

Conformance with EMC Directive 2014/30/EU

Mounting

Mounting type

DIN rail mounting

PSM-EG-RS232/RS485-P/2D - Interface converter



2761392

<https://www.phoenixcontact.com/us/products/2761392>

Classifications

UNSPSC

UNSPSC 21.0	43222604
-------------	----------

2761392

<https://www.phoenixcontact.com/us/products/2761392>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com