


PI-EX-RTD - Signal converter



2865311

<https://www.phoenixcontact.com/us/products/2865311>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i temperature transducer: converts measured values from resistance thermometers installed in the Ex area to a 0/4 mA ... 20 mA signal for driving a non-intrinsically safe load. Freely programmable. 3-way electrical isolation.

Commercial data

Item number	2865311
Packing unit	1 pc
Sales key	NULL
Product key	DK1XXX
GTIN	4046356460569
Weight per piece (including packing)	128.2 g
Weight per piece (excluding packing)	116.2 g
Customs tariff number	85437090
Country of origin	DE

Technical data

Product properties

Product type	Temperature transmitter
--------------	-------------------------

Electrical properties

Electrical isolation	3-way isolation
----------------------	-----------------

Input data

Measurement

Temperature measuring range	-200 °C ... 850 °C (Range depending on the sensor type)
-----------------------------	---

Output data

Switching:

Configurable/programmable	no
---------------------------	----

Signal

Configurable/programmable	Yes
---------------------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
---------------------------------	------------------

Approvals

ATEX

Identification	⊕ II (1) G [Ex ia Ga] IIC
	⊕ II (1) D [Ex ia Da] IIIC
	⊕ II 3 (1) G Ex nA ic [ia Ga] IIC T4 Gc

EAC Ex

Identification	Ex [Ex ia Ga] IIC
Certificate	RU C-DE.AB72.B.00097/19

Standards and regulations

Electrical isolation	3-way isolation
----------------------	-----------------

PI-EX-RTD - Signal converter

2865311

<https://www.phoenixcontact.com/us/products/2865311>



Classifications

UNSPSC

UNSPSC 21.0	41112100
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------