

UKK 4-FS/FS - Feed-through terminal block



2771133

<https://www.phoenixcontact.com/us/products/2771133>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 400 V, nominal current: 20 A, connection method: Spade connection, 1st and 2nd level, Rated cross section: 4 mm², cross section: 0.5 mm² - 6 mm², mounting type: NS 35/7,5, NS 35/15, NS 32, color: gray

Commercial data

Item number	2771133
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE05
Product key	BE511X
GTIN	4017918068219
Weight per piece (including packing)	11.67 g
Weight per piece (excluding packing)	11.67 g
Customs tariff number	85369010
Country of origin	PL

UKK 4-FS/FS - Feed-through terminal block



2771133

<https://www.phoenixcontact.com/us/products/2771133>

Technical data

Product properties

Product type	Feed-through terminal block
Product family	UK
Number of connections	8
Number of rows	2
Potentials	2

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	1.02 W

Connection data

Number of connections per level	4
Nominal cross section	4 mm ²

1st and 2nd level

Connection method	Spade connection
Spade connection	6.3/2.8 x 0.8 mm
Conductor cross-section rigid	0.5 mm ² ... 6 mm ²
Cross section AWG	20 ... 10 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 6 mm ²
Conductor cross-section, flexible [AWG]	20 ... 10 (converted acc. to IEC)
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 6 mm ²
Nominal cross section	4 mm ²
Nominal current	20 A (current data for slip-on connections in acc. with DIN 61210 are also dependent on nominal size, material, insulation of the sleeve and conductor cross-section.)
Maximum load current	20 A (current data for slip-on connections in acc. with DIN 61210 are also dependent on nominal size, material, insulation of the sleeve and conductor cross-section.)
Nominal voltage	400 V (voltage data for slip-on connections in acc. with DIN 61210 are also dependent on nominal size, material, insulation of the sleeve and conductor cross-section.)

Dimensions

Width	6.2 mm
End cover width	1.5 mm
Height	72 mm
Depth on NS 32	64 mm
Depth on NS 35/7,5	59 mm

UKK 4-FS/FS - Feed-through terminal block



2771133

<https://www.phoenixcontact.com/us/products/2771133>

Depth on NS 35/15	66.5 mm
-------------------	---------

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

UKK 4-FS/FS - Feed-through terminal block




2771133

<https://www.phoenixcontact.com/us/products/2771133>

Drawings

Circuit diagram




UKK 4-FS/FS - Feed-through terminal block

2771133

<https://www.phoenixcontact.com/us/products/2771133>

Circuit diagram



- 1 = Cover
- 2 = Fixed bridge
- 3 = Insertion bridge
- 4 = Isolator bridge bar
- 5 = Isolator bridge
- 6 = Test socket, for test pick-off with MPS test plug or RPS reducing plug
- 7 = Test socket, insulated, can only be used above FBI, KB, ISSBI

UKK 4-FS/FS - Feed-through terminal block



2771133

<https://www.phoenixcontact.com/us/products/2771133>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2771133>



EAC

Approval ID: RU C-DE.BL08.B.00541



cULus Recognized

Approval ID: E60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	300 V	20 A	-	-
C				
	300 V	20 A	-	-

UKK 4-FS/FS - Feed-through terminal block



2771133

<https://www.phoenixcontact.com/us/products/2771133>

Classifications

ECLASS

ECLASS-13.0	27250102
ECLASS-15.0	27250102

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UKK 4-FS/FS - Feed-through terminal block



2771133

<https://www.phoenixcontact.com/us/products/2771133>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.085 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com