


PI-EX-AIS - Input signal conditioner



2865696

<https://www.phoenixcontact.com/us/products/2865696>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i analog input: input signal conditioner, HART-transparent. Transmits 4 mA ... 20 mA signals from externally supplied measuring transducers installed in the Ex area to a load in the safe area. 3-way electrical isolation (input/output/supply).

Commercial data

Item number	2865696
Packing unit	1 pc
Sales key	C430
Product key	DK1XXX
GTIN	4046356483605
Weight per piece (including packing)	96.3 g
Weight per piece (excluding packing)	93.9 g
Customs tariff number	85437090
Country of origin	DE

PI-EX-AIS - Input signal conditioner



2865696

<https://www.phoenixcontact.com/us/products/2865696>

Technical data

Product properties

Product type	Signal conditioner
Application	Analog IN
No. of channels	1

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Electrical isolation	3-way isolation
Electrical isolation between input and output	yes
Step response (10-90%)	< 600 μ s (for 4 mA ... 20 mA step)
Maximum temperature coefficient	< 0.01 %/K
Maximum transmission error	< 0.2 % (of final value)
Transmission error, typical	< 0.1 % (of final value)

Electrical isolation Input/output/power supply

Rated insulation voltage	300 V _{rms}
Test voltage	2.5 kV AC (50 Hz, 60 s)
Insulation	Safe isolation in accordance with IEC/EN 61010-1

Electrical isolation Input/output

Electrical isolation	375 V (Peak value in accordance with IEC/EN 60079-11)
----------------------	---

Electrical isolation Input/power supply

Electrical isolation	375 V (Peak value in accordance with IEC/EN 60079-11)
----------------------	---

Supply

Supply voltage range	19.2 V DC ... 30 V DC
Max. current consumption	< 36 mA (at 24 V)
Power dissipation	< 0.9 W (at 24 V DC / 20 mA)

Input data

Signal: Current

Description of the input	intrinsically safe
Number of inputs	1
Current input signal	0 mA ... 20 mA 4 mA ... 20 mA
Voltage drop	< 3.5 V

Output data

Signal: Current

PI-EX-AIS - Input signal conditioner

2865696

<https://www.phoenixcontact.com/us/products/2865696>

Number of outputs	1
Current output signal	0 mA ... 20 mA (active)
	4 mA ... 20 mA (active)
	0 mA ... 20 mA (14 ... 26 V ext. source voltage)
	4 mA ... 20 mA (14 ... 26 V ext. source voltage)
Load/output load current output	$\leq 600 \Omega$ (at 20 mA)
	$< 525 \Omega$ (at 22.5 mA)
Output ripple	$< 20 \text{ mV}_{\text{rms}}$
Output behavior in the event of an error	0 mA (Cable break in the input)
	0 mA (Cable short-circuit in the input)

Ex data

Safety data

Max. voltage U_i	30 V
Max. current I_i	150 mA
Max. inductance L_i	negligible
Max. capacitance C_i	Negligible
Safety-related maximum voltage U_m	253 V AC

Interfaces


Data communication (bypass)

HART function	Yes
Protocols supported	HART-transparent

Signaling

Status display	LED supply voltage, PWR (green)
----------------	---------------------------------

Dimensions

Dimensional drawing	
Width	12.4 mm
Height	79 mm
Depth	118.4 mm

Material specifications

Color	green (RAL 6021)
Flammability rating according to UL 94	V0
Housing material	PBT and polyamide PA non-reinforced

PI-EX-AIS - Input signal conditioner



2865696

<https://www.phoenixcontact.com/us/products/2865696>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)

Approvals

CE

Certificate	CE-compliant
Note	and EN 61326

ATEX

Identification	⊕ II (1) G [Ex ia Ga] IIC
	⊕ II (1) D [Ex ia Da] IIIC
	⊕ II 3 (1) G Ex nA [ia Ga] IIC T4 Gc

Safety Integrity Level (SIL, IEC 61508)

Identification	2
----------------	---

EAC Ex

Identification	Ex [Ex ia Ga] IIC
Certificate	RU C-DE.AB72.B.00097/19

Standards and regulations

Electrical isolation	3-way isolation
----------------------	-----------------

PI-EX-AIS - Input signal conditioner


2865696

<https://www.phoenixcontact.com/us/products/2865696>



Drawings

Dimensional drawing




PI-EX-AIS - Input signal conditioner

2865696

<https://www.phoenixcontact.com/us/products/2865696>

Block diagram



PI-EX-AIS - Input signal conditioner



2865696

<https://www.phoenixcontact.com/us/products/2865696>

Classifications

ECLASS

ECLASS-13.0

27210120

ETIM

ETIM 9.0

EC002653

UNSPSC

UNSPSC 21.0

39121000

PI-EX-AIS - Input signal conditioner



2865696

<https://www.phoenixcontact.com/us/products/2865696>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com