

FLX ASI DI 4 M8 - Distributed I/O device



2773403

<https://www.phoenixcontact.com/us/products/2773403>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



AS-i digital input module, single slave, 4 digital inputs, 24 V DC, 2, 3 and 4-conductor connection method, IP67 protection

Product description

The digital Fieldline Extension AS-Interface M8 input modules with IP67 housing protection make it possible to connect digital sensors to the AS-i using M8 connectors.

The modules are connected to AS-i with an M12 connector using the SPEEDCON connection method.

Your advantages

- M8 connection technology for the I/Os
- M12 connection technology with SPEEDCON fast locking system for the AS-Interface connection
- Optimized for 30 mm mounting profile

Commercial data

Item number	2773403
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR03
Product key	DRI631
GTIN	4046356156585
Weight per piece (including packing)	102.3 g
Weight per piece (excluding packing)	85 g
Customs tariff number	85176200
Country of origin	SG

FLX ASI DI 4 M8 - Distributed I/O device



2773403

<https://www.phoenixcontact.com/us/products/2773403>

Technical data

Dimensions

Width	30 mm
Height	26 mm
Depth	103 mm
Drill hole spacing	93 mm

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Material specifications

Color	black
-------	-------

Interfaces

AS-Interface

Connection method	M12 connector, A-coded
Designation connection point	AS-i
Number of positions	2
Transmission speed	167 kbps

System properties

Programming data

ID code (dec.)	0
----------------	---

Input data

Digital:

Input name	Digital inputs
Description of the input	IEC 61131-2 Type 2
Number of inputs	4
Connection method	M8 connector
Connection technology	2-, 3-conductor

Product properties

Product type	I/O component
Product family	Fieldline
Type	Block design
Mounting position	any
No. of channels	4

FLX ASI DI 4 M8 - Distributed I/O device



2773403

<https://www.phoenixcontact.com/us/products/2773403>

Connection data

Connection method	M8 connector
-------------------	--------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Degree of protection	IP65/IP67
Ambient temperature (storage/transport)	-25 °C ... 85 °C

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	direct screw connection
	Panel mounting
Mounting position	any

FLX ASI DI 4 M8 - Distributed I/O device




2773403

<https://www.phoenixcontact.com/us/products/2773403>

Drawings

Connection diagram



FLX ASI DI 4 M8 - Distributed I/O device



2773403

<https://www.phoenixcontact.com/us/products/2773403>

Classifications

UNSPSC

UNSPSC 21.0	32151602
-------------	----------

FLX ASI DI 4 M8 - Distributed I/O device



2773403

<https://www.phoenixcontact.com/us/products/2773403>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com