

QUINT-DIODE/48DC/40 - Redundancy module, with protective coating



2866585

<https://www.phoenixcontact.com/us/products/2866585>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

QUINT-DIODE/48DC/40 redundancy module



Commercial data

Item number	2866585
Packing unit	1 pc
Sales key	NULL
Product key	CMRP44
GTIN	4046356494458
Weight per piece (including packing)	679 g
Weight per piece (excluding packing)	679 g
Customs tariff number	85049090
Country of origin	CN

QUINT-DIODE/48DC/40 - Redundancy module, with protective coating



2866585

<https://www.phoenixcontact.com/us/products/2866585>

Technical data

Input data

DC operation

Input voltage	48 V DC (U_N)
	< 60 V DC (U_{max})
Input voltage range	10 V DC ... 60 V DC
Input voltage range DC	10 V DC ... 60 V DC
Voltage type of supply voltage	DC
Reverse polarity protection	yes, < 120 V
Nominal input current (I_N)	2x 20 A
	1x 40 A
Maximum current I_{max}	2x 19 A (6 mm ² at 40°C)
	1x 39 A (6 mm ² at 40°C)
	2x 16 A (6 mm ² at 60°C)
	1x 32 A (6 mm ² at 60°C)
	2x 27 A (10 mm ² at 40°C)
	1x 54 A (10 mm ² at 40°C)
	2x 21 A (10 mm ² at 60°C)
	1x 43 A (10 mm ² at 60°C)
	2x 30 A (16 mm ² at 40 °C)
	1x 60 A (16 mm ² at 40 °C)
	2x 24 A (16 mm ² at 60°C)
	1x 48 A (16 mm ² at 60°C)
	Nominal input current (I_N)
1x 40 A	
Maximum current I_{max}	2x 17 A (6 mm ² at 40°C for potentially explosive areas: Class I, Div. 2, Groups A, B, C, D; T4)
	1x 35 A (6 mm ² at 40°C for potentially explosive areas: Class I, Div. 2, Groups A, B, C, D; T4)
	2x 14 A (6 mm ² at 60°C for potentially explosive areas: Class I, Div. 2, Groups A, B, C, D; T4)
	1x 28 A (6 mm ² at 60°C for potentially explosive areas: Class I, Div. 2, Groups A, B, C, D; T4)
	2x 24 A (10 mm ² at 40°C for potentially explosive areas: Class I, Div. 2, Groups A, B, C, D; T4)
	1x 49 A (10 mm ² at 40°C for potentially explosive areas: Class I, Div. 2, Groups A, B, C, D; T4)
	2x 19 A (10 mm ² at 60°C for potentially explosive areas: Class I, Div. 2, Groups A, B, C, D; T4)
	1x 39 A (10 mm ² at 60°C for potentially explosive areas: Class I, Div. 2, Groups A, B, C, D; T4)
	2x 27 A (16 mm ² at 40°C for potentially explosive areas: Class I, Div. 2, Groups A, B, C, D; T4)

QUINT-DIODE/48DC/40 - Redundancy module, with protective coating



2866585

<https://www.phoenixcontact.com/us/products/2866585>

	1x 54 A (16 mm ² at 40°C for potentially explosive areas: Class I, Div. 2, Groups A, B, C, D; T4)
	2x 22 A (16 mm ² at 60°C for potentially explosive areas: Class I, Div. 2, Groups A, B, C, D; T4)
	1x 44 A (16 mm ² at 60°C for potentially explosive areas: Class I, Div. 2, Groups A, B, C, D; T4)
Transient surge protection	Transil diode
Voltage drop, input/output	approx. 0.7 V

Output data

Efficiency	> 97 %
Nominal output voltage	47.3 V DC (Input/output voltage drop of 48 V ... 0.7 V)
Nominal output current (I _N)	40 A
Power loss nominal load max.	28 W
Connection in series	no

Connection data

Input

Connection method	Screw connection
Conductor cross-section, rigid min.	0.5 mm ²
Conductor cross-section, rigid max.	16 mm ²
Conductor cross-section flexible min.	0.5 mm ²
Conductor cross-section flexible max.	10 mm ²
Conductor cross-section AWG min.	20
Conductor cross-section AWG max.	6
Stripping length	10 mm
Screw thread	M4
Tightening torque, min	1.2 Nm
Tightening torque max	1.5 Nm

Output

Connection method	Screw connection
Conductor cross-section, rigid min.	0.5 mm ²
Conductor cross-section, rigid max.	16 mm ²
Conductor cross-section flexible min.	0.5 mm ²
Conductor cross-section flexible max.	10 mm ²
Conductor cross-section AWG min.	20
Conductor cross-section AWG max.	6
Stripping length	10 mm
Screw thread	M4
Tightening torque, min	1.2 Nm
Tightening torque max	1.5 Nm

Electrical properties

QUINT-DIODE/48DC/40 - Redundancy module, with protective coating



2866585

<https://www.phoenixcontact.com/us/products/2866585>

Standard – Electronic equipment for use in electrical power installations and their assembly into electrical power installations	EN 50178/VDE 0160 (PELV)
Standard - Electrical safety	EN 60950-1/VDE 0805 (SELV)

Approvals

UL approvals	UL/C-UL listed UL 508
	UL/C-UL Recognized UL 60950-1
	UL/C-UL Listed UL 1604 Class I, Division 2, Groups A, B, C, D

Conformity/Approvals

ATEX	⊕ II 3 G Ex nA II T4
------	----------------------

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Low Voltage Directive	Conformance with Low Voltage Directive 2014/35/EC
EMC requirements for noise emission	EN 61000-6-3
	EN 61000-6-4
EMC requirements for noise immunity	EN 61000-6-1
	EN 61000-6-2

Noise emission

Standards/regulations	EN 55011
-----------------------	----------

QUINT-DIODE/48DC/40 - Redundancy module, with protective coating



2866585

<https://www.phoenixcontact.com/us/products/2866585>

Classifications

UNSPSC

UNSPSC 21.0	32151504
-------------	----------

QUINT-DIODE/48DC/40 - Redundancy module, with protective coating



2866585

<https://www.phoenixcontact.com/us/products/2866585>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com