

RF-TRAB - Surge protection device



2782135

<https://www.phoenixcontact.com/us/products/2782135>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Attachment plug with replaceable surge protection for coaxial signal interfaces, transmission capacity ≤ 200 W. Connection: UHF female/female.



Commercial data

Item number	2782135
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	CL03
Product key	CL3316
GTIN	4017918069377
Weight per piece (including packing)	80.18 g
Weight per piece (excluding packing)	80.18 g
Customs tariff number	85363010
Country of origin	DE

RF-TRAB - Surge protection device



2782135

<https://www.phoenixcontact.com/us/products/2782135>

Technical data

Notes

General

Note	To meet the discharge conditions for DC voltages, please note the following information: "The surge protective device should be used together with a transmitter unit, which shuts down in the event of a short-circuit."
------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Product properties

Product type	Surge protection for transceiver systems
IEC test classification	C2
	C3
	D1
Type	Intermediate plug
Surge protection fault message	none

Insulation characteristics

Overvoltage category	III
----------------------	-----

Connection data

Connection method	UHF connector
-------------------	---------------

Dimensions

Width	60.5 mm
Height	40 mm
Depth	18.1 mm

Material specifications

Housing material	Nickel-plated brass
------------------	---------------------

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Direction of action	Line-Shield/Earth Ground
Maximum continuous operating voltage U_C	130 V AC
Nominal current I_N	10 A (25 °C)
Operating effective current I_C at U_C	$\leq 1 \mu\text{A}$
Protective conductor current I_{PE}	$\leq 1 \mu\text{A}$
Nominal discharge current I_n (8/20) μs (line-ground)	10 kA
Nominal discharge current I_n (8/20) μs (line-shield)	10 kA
Pulse discharge current I_{imp} (10/350) μs (line-earth)	2.5 kA

RF-TRAB - Surge protection device



2782135

<https://www.phoenixcontact.com/us/products/2782135>

Pulse discharge current I_{imp} (10/350) μ s (line-shield)	2.5 kA
Total surge current (8/20) μ s	10 kA
Impulse discharge current (10/350) μ s, peak value I_{imp}	2.5 kA
Output voltage limitation at 1 kV/ μ s (line-earth) spike	≤ 600 V
Output voltage limitation at 1 kV/ μ s (line-shield) spike	≤ 600 V
Output voltage limitation at 1 kV/ μ s (line-earth) static	≤ 600 V
Output voltage limitation at 1 kV/ μ s (line-shield) static	≤ 600 V
Voltage protection level U_p (line-earth)	≤ 600 V
Voltage protection level U_p (line-shield)	≤ 600 V
Response time t_A (line-earth)	≤ 100 ns
Response time t_A (line-shield)	≤ 100 ns
Input attenuation aE, asym.	typ. 0.3 dB (≤ 250 MHz / 50 Ω)
Cut-off frequency f_g (3 dB), asym. (shield) in 50 Ω system	typ. 950 MHz
Voltage standing wave ratio VSWR in a 50 Ω system	≤ 1.20 (≤ 80 MHz)
	≤ 1.50 (≤ 200 MHz)
Permissible HF power P_{max} at VSWR = xx (50 ohm system)	300 W (VSWR = 1.1)
	80 W (VSWR = ∞)
Capacity	typ. 2 pF
Surge protection fault message	none
Impulse durability (line-earth)	C2 - 10 kV / 5 kA
	D1 - 2.5 kA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... -90 °C
Altitude	≤ 2000 m (amsl)

Standards and regulations

Standards/specifications	IEC 61643-21
Note	2000-09

Mounting


Mounting type	Connection-specific intermediate plugging
---------------	-------------------------------------------

2782135

<https://www.phoenixcontact.com/us/products/2782135>

Drawings

Diagram




RF-TRAB - Surge protection device

2782135

<https://www.phoenixcontact.com/us/products/2782135>



Circuit diagram



RF-TRAB - Surge protection device



2782135

<https://www.phoenixcontact.com/us/products/2782135>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com