

RF-TRAB-A1 - Surge protection device



2782575

<https://www.phoenixcontact.com/us/products/2782575>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screw-on module with surge protection, for coaxial signal interfaces with floating shield, transmission power 200 W, connection: UHF connector

Commercial data

Item number	2782575
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	CL3316
GTIN	4017918069629
Weight per piece (including packing)	113.11 g
Weight per piece (excluding packing)	101.948 g
Customs tariff number	85363010
Country of origin	DE

RF-TRAB-A1 - Surge protection device



2782575

<https://www.phoenixcontact.com/us/products/2782575>

Technical data

Product properties

Product type	Surge protection for transceiver systems
IEC test classification	C2
	C3
	D1
Type	Intermediate plug

Connection data

Connection method	UHF connector
-------------------	---------------

Material specifications

Housing material	Aluminum
------------------	----------

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Direction of action	Line-Shield/Earth Ground
Maximum continuous operating voltage U_C	130 V AC
Maximum continuous voltage U_C (line-earth)	130 V AC
Protective conductor current I_{PE}	$\leq 2 \mu A$
Nominal discharge current I_n (8/20) μs (line-ground)	5 kA
Nominal discharge current I_n (8/20) μs (line-shield)	5 kA
Total surge current (8/20) μs	10 kA
Output voltage limitation at 1 kV/ μs (line-earth) spike	$\leq 450 V$
Output voltage limitation at 1 kV/ μs (line-shield) spike	$\leq 650 V$
Output voltage limitation at 1 kV/ μs (line-earth) static	$\leq 450 V$
Output voltage limitation at 1 kV/ μs (line-shield) static	$\leq 650 V$
Voltage protection level U_p (line-earth)	$\leq 450 V$
Voltage protection level U_p (line-shield)	$\leq 650 V$
Response time t_A (line-earth)	$\leq 100 ns$
Response time t_A (line-shield)	$\leq 100 ns$
Input attenuation aE, asym.	0.3 dB ($\leq 150 MHz$)
Cut-off frequency f_g (3 dB), asym. (shield) in 50 Ω system	typ. 550 MHz
Voltage standing wave ratio VSWR in a 50 Ω system	≤ 1.20 ($\leq 80 MHz$)
Permissible HF power P_{max} at VSWR = xx (50 ohm system)	300 W (VSWR = 1.1)
	80 W (VSWR = ∞)
Impulse durability (line-earth)	C2 - 10 kV / 5 kA
	D1 - 2.5 kA

RF-TRAB-A1 - Surge protection device



2782575

<https://www.phoenixcontact.com/us/products/2782575>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 80 °C

Standards and regulations

Standards Information technology specification

Standards/regulations	IEC 61643-21
	IEC 61643-21
Standards/specifications	IEC 61643-21
Note	2000

Mounting

Mounting type	Connection-specific intermediate plugging
---------------	---

RF-TRAB-A1 - Surge protection device




2782575

<https://www.phoenixcontact.com/us/products/2782575>

Drawings

Diagram




RF-TRAB-A1 - Surge protection device

2782575

<https://www.phoenixcontact.com/us/products/2782575>



Circuit diagram



RF-TRAB-A1 - Surge protection device



2782575

<https://www.phoenixcontact.com/us/products/2782575>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com