RAD-CAB-EF393- 3M - Antenna cable

2867649

https://www.phoenixcontact.com/us/products/2867649

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Antenna cable, outside diameter: 10 mm (0.4 in.), inner conductor: stranded, attenuation: 1.0 / 1.8 / 3.1 dB at 0.9 / 2.4 / 5.8 GHz, connection: 2 x N (male), cable length: 3 m (10 ft.)



The figure shows a version of the product

Your advantages

- Halogen-free
- Easy installation, thanks to flexible inner conductor
- Flame-retardant
- UV resistant
- Oil-resistant
- For outdoor installation

Commercial data

Item number	2867649
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN23
Product key	DNN2Z1
GTIN	4017918939014
Weight per piece (including packing)	600 g
Weight per piece (excluding packing)	590 g
Customs tariff number	85442000
Country of origin	PL

Technical data

Product properties

Product type	Coaxial cable

Electrical properties

Frequency range	0.3 GHz ... 6 GHz
Impedance	50 Ω

Connection data

Connector connection

Connection method	N (male)
Notes	Both sides
Connection method	N (male)

Material specifications

Outer sheath, material	RADOX®(LSFH)

Cable/line

Cable length	3 m
Cable type	EF 393
External cable diameter	10.00 mm
Outer sheath, material	RADOX®(LSFH)
External sheath, color	black
Bending radius, long-term	50.00 mm
868 / 900 MHz	~ 1 dB (Attenuation of entire cable)
2.4 GHz	~ 1.8 dB (Attenuation of entire cable)
5.8 GHz	~ 3.1 dB (Attenuation of entire cable)
Resistance to oil	very good oil and chemical resistance

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (storage/transport)	-40 °C ... 105 °C
Ambient temperature (assembly)	-20 °C ... 60 °C
Resistance to oil	very good oil and chemical resistance

Approvals

CE

Certificate	CE-compliant

Standards and regulations

Resistance to oil	very good oil and chemical resistance

Standard designation	Flame retardancy
Standards/specifications	DIN EN 60332-1-2
	UL 1581
Standard designation	Halogen-free
Standards/specifications	IEC 60754
Standard designation	UV resistance
Standards/specifications	IEC 60068-2-5

Mounting

Assembly note	Outdoors and indoors

Classifications

ECLASS

ECLASS-13.0	27060310

ETIM

ETIM 9.0	EC001682

UNSPSC

UNSPSC 21.0	26121600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9a15fa20-7775-4ad6-abbe-4ce2c6fadfb1

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com