

PSM-LWL-KDL-980/1000 - FO cable



2799283

<https://www.phoenixcontact.com/us/products/2799283>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Polymer fiber cable, duplex 980/1000 μm , light-weight version for indoor installation, by the meter, without connector

Commercial data

Item number	2799283
Packing unit	1 m
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DNC231
GTIN	4017918074005
Weight per piece (including packing)	7.56 g
Weight per piece (excluding packing)	7.56 g
Customs tariff number	85447000
Country of origin	DE

PSM-LWL-KDL-980/1000 - FO cable



2799283

<https://www.phoenixcontact.com/us/products/2799283>

Technical data

Product properties

Product type	Data cable by the meter
Number of positions	2

Electrical properties

Transmission medium	Polymer fiber
---------------------	---------------

Interfaces

Signal	INTERBUS
	PROFIBUS
	Point-to-point
	Ethernet
	RS-485

Dimensions

External dimensions

External diameter min.	2.2 mm
External diameter max.	4.4 mm

Material specifications

Color (Single-core wire)	black (RAL 9005)
--------------------------	------------------

Cable/line

Cable length	variable
Cable weight	7.8 kg/km
Cable type	Polymer fiber
Cable abbreviation	CA-1D2Y2P 980/1000 160A 10
Single wire, material	PE
Individual wire diameter	2.2 mm ±0.07 mm
Bending radius, single element	30 mm (Short-term)
	30 mm (Short-term)
Bending radius, entire cable	65 mm (Short-term)
	65 mm (Short-term)
Bending radius	30 mm (Short-term)
	30 mm (permanent)
	65 mm (Short-term)
	65 mm (permanent)
Tensile strength short-term/long-term	40 N / 10 N
Lateral pressure short term	60 N/cm
Lateral pressure, long-term	10 N/cm
660 nm	230 dB/km

PSM-LWL-KDL-980/1000 - FO cable



2799283

<https://www.phoenixcontact.com/us/products/2799283>

FO cable

Fiber	Polymer fiber, 980/1000 µm
-------	----------------------------

Mechanical properties

Tensile strength short-term/long-term	40 N / 10 N
---------------------------------------	-------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Altitude	5000 m

Mounting

cable layer type	Indoors
------------------	---------

PSM-LWL-KDL-980/1000 - FO cable



2799283

<https://www.phoenixcontact.com/us/products/2799283>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com