

LM-S-C-3LS - Lightning monitoring system



2800617

<https://www.phoenixcontact.com/us/products/2800617>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



O/E module for live monitoring system for the continuous detection and evaluation of lightning strikes.

Your advantages

- Replacement O/E module for evaluation unit
- Connection of up to 3 LM-S sensors
- Status and diagnostic display via evaluation unit

Commercial data

Item number	2800617
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	CLB312
GTIN	4046356615280
Weight per piece (including packing)	695.5 g
Weight per piece (excluding packing)	695.5 g
Country of origin	DE

LM-S-C-3LS - Lightning monitoring system



2800617

<https://www.phoenixcontact.com/us/products/2800617>

Technical data

Product properties

Product type	O/E module
Product family	LM-S

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Evaluation unit

Operating voltage	3.3 V DC
	+ 5 V DC
	- 5 V DC
Detectable values (current strength)	5.00 kA ... 400.00 kA

Evaluation unit Sensor interfaces

Interface	O/E module
Number of ports	3

O/E converter

Interface	Fiber optic interface
Number of ports	3
Connection method	B-FOC (ST®)

O/E converter Function

Basic functions	Plug-in I/O module as fiber optic port
Status and diagnostic indicators	Via LM-S evaluation unit

Sensor

Detectable values (current strength)	± 5.00 kA ... 400.00 kA
--------------------------------------	-------------------------

Typical characteristics

Rated current I_n	300 mA
---------------------	--------

Dimensions

Width	70 mm
Height	185 mm
Depth	181.5 mm

Material specifications

Color	silver-colored
	black (RAL 9005)
Housing material	Stainless steel 1.4016

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-30 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 4000 m (amsl)
Permissible humidity (operation)	30 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	30 % ... 95 % (non-condensing)

Standards and regulations

Standards/specifications	EN 61326-1
Note	2013

Mounting

Mounting type	Pluggable (slot)
---------------	------------------

LM-S-C-3LS - Lightning monitoring system



2800617

<https://www.phoenixcontact.com/us/products/2800617>

Classifications

ECLASS

ECLASS-13.0	27170192
ECLASS-15.0	27170192

ETIM

ETIM 10.0	EC002495
-----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

LM-S-C-3LS - Lightning monitoring system



2800617

<https://www.phoenixcontact.com/us/products/2800617>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com