

ME B-12,5 MSTBO PUWH - Filler plug



2869113

<https://www.phoenixcontact.com/us/products/2869113>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Filler plug for unoccupied terminal points (MSTBO), width: 10 mm, height: 19.06 mm, depth: 12.29 mm, color: white (similar RAL 9010)

Figure shows standard item in light gray

Your advantages

- Easy, tool-free mounting
- Flammability rating V0 in accordance with UL 94

Commercial data

Item number	2869113
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ACHAAZ
GTIN	4017918923419
Weight per piece (including packing)	0.85 g
Weight per piece (excluding packing)	0.85 g
Country of origin	DE

ME B-12,5 MSTBO PUWH - Filler plug



2869113

<https://www.phoenixcontact.com/us/products/2869113>

Technical data

Product properties

Product type	Filler plug
Housing type	DIN rail housing
Housing series	ME
Product family	ME 12,5..
Ventilation openings present	no

Dimensions

Width	10 mm
Height	19.06 mm
Depth	12.29 mm

Material specifications

Color (Housing)	white (RAL 9010)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Housing material	PA

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.15 mm (10 Hz ... 58.1 Hz)
Acceleration	2g (58.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20 N

Mechanical strength / tumbling barrel

Specification	IEC 60998-1:2002-12
Height of fall	50 cm

ME B-12,5 MSTBO PUWH - Filler plug



2869113

<https://www.phoenixcontact.com/us/products/2869113>

Frequency	10
-----------	----

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Half-sine
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

Degree of protection (IP code)

Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
---------------	---

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Latching
---------------	----------

ME B-12,5 MSTBO PUWH - Filler plug



2869113

<https://www.phoenixcontact.com/us/products/2869113>

Classifications

ECLASS

ECLASS-13.0

27190605

ETIM

ETIM 9.0

EC002779

UNSPSC

UNSPSC 21.0

31261500

ME B-12,5 MSTBO PUWH - Filler plug



2869113

<https://www.phoenixcontact.com/us/products/2869113>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com