

IB IL EX-IS PWR IN-PAC - Modular power terminal



2869910

<https://www.phoenixcontact.com/us/products/2869910>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Inline power terminal for power supply to intrinsically safe I/O terminals



Your advantages

- Diagnostic LEDs (standard load, high load, overload) provide direct feedback regarding the capacity
- Electronic overload protection
- 1000 mA for logic supply circuit (UL)
- 1000 mA for I/O supply (UEX)
- The design requires a gap of 50 mm between intrinsically safe and non-intrinsically safe connections
- Electrical isolation between Inline I/O station and intrinsically safe I/O termination devices

Commercial data

Item number	2869910
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI1E1
GTIN	4046356470193
Weight per piece (including packing)	427.6 g
Weight per piece (excluding packing)	292 g
Customs tariff number	85389099
Country of origin	US

IB IL EX-IS PWR IN-PAC - Modular power terminal



2869910

<https://www.phoenixcontact.com/us/products/2869910>

Technical data

Dimensions

Dimensional drawing	
Width	48.8 mm
Height	119.9 mm
Depth	70.4 mm

Notes

Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

Material specifications

Color	blue
-------	------

Interfaces

Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps

Product properties

Product type	I/O component
Product family	Inline
Type	modular
	Inline

Electrical properties

Potentials

Power consumption	max. 8 W
-------------------	----------

Potentials: Voltage supply for IB IL EX-IS...IO... modules U_V

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 1.5 A
	max. 2 A

Potentials: Communications power (U_L)

IB IL EX-IS PWR IN-PAC - Modular power terminal



2869910

<https://www.phoenixcontact.com/us/products/2869910>

Supply voltage	5 V DC (via voltage jumper)
Power supply	1 A (max.)

Potentials: U_{EX} supply to I/O terminals

Supply voltage	28 V DC ±5 %
Power supply	max. 1 A

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Degree of protection	IP20
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)

Standards and regulations

Protection class	III (VDE 0106, IEC 60536)
------------------	---------------------------

Approvals

Ex data

ATEX	⊕ II 3G Ex ec IIC T4 Gc Sira 10ATEX2130X
IECEX	Ex ec IIC T4 Gc IECEX SIR 10.0085X
UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D, T4

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Ex data

Safety data

Safety-related maximum voltage U _m	253 V
---	-------

IB IL EX-IS PWR IN-PAC - Modular power terminal




2869910


<https://www.phoenixcontact.com/us/products/2869910>

Drawings

Dimensional drawing



Connection diagram



IB IL EX-IS PWR IN-PAC - Modular power terminal



2869910

<https://www.phoenixcontact.com/us/products/2869910>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2869910>



ATEX

Approval ID: Sira 10ATEX2130X

IB IL EX-IS PWR IN-PAC - Modular power terminal



2869910

<https://www.phoenixcontact.com/us/products/2869910>

Classifications

ECLASS

ECLASS-13.0

27242610

ETIM

ETIM 9.0

EC001600

UNSPSC

UNSPSC 21.0

32151600

IB IL EX-IS PWR IN-PAC - Modular power terminal



2869910

<https://www.phoenixcontact.com/us/products/2869910>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com