

# IB IL AO 4/8/U/BP-2MBD-PAC - Analog module



2878052

<https://www.phoenixcontact.com/us/products/2878052>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Analog output terminal, Analog outputs: 8, 0 V ... 10 V, -10 V ... 10 V, 0 V ... 5 V, -5 V ... 5 V, connection technology: 2-conductor, transmission speed in the local bus: 2 Mbps, degree of protection: IP20, including Inline connectors and marking fields

## Product description

Inline terminals with "2 MBD" added to their item designation work with a transmission speed of 2 Mbps. These terminal blocks are discontinued or no longer in the range. If you require this transmission speed, please ask your local Phoenix Contact representative. If you can work with a transmission speed of 500 kbps, select as a replacement the corresponding variant that does not have "2MBD" added to its item designation. Please note that a uniform transmission speed must always be used within one inline station. The terminal is designed for use within an Inline station. It is used to output analog voltage signals. The output values are displayed as 8-bit or 16-bit values.

## Your advantages

- 8 analog bipolar outputs
- Connection of actuators in 2-conductor technology
- The channels are parameterized independently of one another via the bus system
- Output values can be represented in four different formats
- Diagnostic and status indicators

## Commercial data

Item number	2878052
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI142
GTIN	4046356048453
Weight per piece (including packing)	252 g
Weight per piece (excluding packing)	215 g
Customs tariff number	85389091
Country of origin	DE

# IB IL AO 4/8/U/BP-2MBD-PAC - Analog module




2878052

<https://www.phoenixcontact.com/us/products/2878052>

## Technical data

### Dimensions

Dimensional drawing	
Width	48.8 mm
Height	136.8 mm
Depth	71.5 mm

### Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

### Interfaces

Inline local bus

Number of interfaces	2
Connection method	Inline data jumper
Transmission speed	2 Mbps
Transmission physics	Copper

### System properties

Programming data (LocalbusSlave)

Length code (hex)	05
ID code (dec.)	223
Length code (dec)	05
Process data channel	80 bit
Input address area	10 Byte
Output address area	10 Byte
Parameter channel (PCP)	2 Byte
Register length (bus)	96 bit

Fieldbus data telegram (PROFIBUS)

Required parameter data	27 Byte
Required configuration data	5 Byte

# IB IL AO 4/8/U/BP-2MBD-PAC - Analog module



2878052

<https://www.phoenixcontact.com/us/products/2878052>

## Output data

### Analog:

Output name	Analog outputs
Connection technology	2-conductor
Note regarding the connection technology	shielded
Number of outputs	8
D/A converter resolution	16 bit
Protective circuit	Transient protection of outputs
Data formats	IB IL, IB ST, IB RT, standardized representation, S7 compatible
Representation of output values	16 bits (15 bits + sign)
Process data update	< 2 ms (depends on operating mode)
Load/output load current output	> 2 k $\Omega$
Voltage output signal	0 V ... 10 V -10 V ... 10 V 0 V ... 5 V -5 V ... 5 V
Load/output load voltage output	> 2 k $\Omega$ 0.05 %

## Product properties

Product type	I/O component
Product family	Inline
Type	modular
Scope of supply	including Inline connectors and marking fields

### Insulation characteristics

Overvoltage category	II (IEC 60664-1, EN 60664-1)
Pollution degree	2 (IEC 60664-1, EN 60664-1)

## Electrical properties

Maximum power dissipation for nominal condition	2.8 W
---	-------

### Potentials: Communications power ( $U_L$ )

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 120 mA typ. 100 mA

### Potentials: Supply of analog modules ( $U_{ANA}$ )

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 95 mA typ. 72 mA

## Connection data

Connection technology

# IB IL AO 4/8/U/BP-2MBD-PAC - Analog module



2878052

<https://www.phoenixcontact.com/us/products/2878052>

Connection name	Inline connector
-----------------	------------------

## Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

### Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	5g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	25g

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IB IL AO 4/8/U/BP-2MBD-PAC - Analog module



2878052


<https://www.phoenixcontact.com/us/products/2878052>

## Drawings

Dimensional drawing



Connection diagram




# IB IL AO 4/8/U/BP-2MBD-PAC - Analog module

2878052

<https://www.phoenixcontact.com/us/products/2878052>

Block diagram



# IB IL AO 4/8/U/BP-2MBD-PAC - Analog module



2878052

<https://www.phoenixcontact.com/us/products/2878052>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2878052>



**cULus Listed**

Approval ID: E140324

# IB IL AO 4/8/U/BP-2MBD-PAC - Analog module



2878052

<https://www.phoenixcontact.com/us/products/2878052>

## Classifications

### ECLASS

ECLASS-13.0	27242601
ECLASS-15.0	27242601

### ETIM

ETIM 10.0	EC001596
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

2878052

<https://www.phoenixcontact.com/us/products/2878052>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6405fc29-7e34-4d1f-878f-682b91f2a5e2

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)