

RAD-CAB-EF142-5M - Antenna cable



2884525

<https://www.phoenixcontact.com/us/products/2884525>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Antenna cable, outside diameter: 5 mm (0.2 in.), inner conductor: stranded, attenuation: 2.8 / 4.9 / 7.8 dB at 0.9 / 2.4 / 5.8 GHz, connection: 2 x SMA (male), cable length: 5 m (16 ft.)



The figure shows a version of the product

Your advantages

- Halogen-free
- Easy installation, thanks to flexible inner conductor
- Flame-retardant
- UV resistant
- Oil-resistant
- For outdoor installation

Commercial data

Item number	2884525
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNN2Z2
GTIN	4046356114240
Weight per piece (including packing)	292.8 g
Weight per piece (excluding packing)	286.7 g
Customs tariff number	85442000
Country of origin	PL

RAD-CAB-EF142-5M - Antenna cable



2884525

<https://www.phoenixcontact.com/us/products/2884525>

Technical data

Product properties

Product type	Coaxial cable
--------------	---------------

Electrical properties

Frequency range	0.3 GHz ... 6 GHz
Impedance	50 Ω

Connection data

Connection method	SMA (male)
Connection method	SMA (male)

Material specifications

Outer sheath, material	RADOX®(LSFH)
------------------------	--------------

Cable/line

Cable length	5 m
Cable type	EF 142
External cable diameter	5 mm
Outer sheath, material	RADOX®(LSFH)
External sheath, color	blue
Bending radius, long-term	30 mm
868 / 900 MHz	2.8 dB
2.4 GHz	4.9 dB

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (storage/transport)	-40 °C ... 105 °C

RAD-CAB-EF142-5M - Antenna cable



2884525

<https://www.phoenixcontact.com/us/products/2884525>

Classifications

UNSPSC

UNSPSC 21.0	26121606
-------------	----------

RAD-CAB-EF142-5M - Antenna cable



2884525

<https://www.phoenixcontact.com/us/products/2884525>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com