

# RAD-PIG-EF142-PIPE - Adapter cable



2885922

<https://www.phoenixcontact.com/us/products/2885922>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Adapter cable, pigtail 50 cm SMA(m) -> SMA(m) with gasket sleeve to connect the panel antenna to RAD-ISM-2400-...PIPE-... radio systems



## Your advantages

- For connecting the PANEL antenna to PIPE wireless modules
- With gasket sleeve for weather protection

## Commercial data

Item number	2885922
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNN2Z1
GTIN	4046356347518
Weight per piece (including packing)	61.5 g
Weight per piece (excluding packing)	58.3 g
Customs tariff number	85442000
Country of origin	DE

# RAD-PIG-EF142-PIPE - Adapter cable



2885922

<https://www.phoenixcontact.com/us/products/2885922>

## Technical data

### Product properties

Product type	Coaxial cable
--------------	---------------

### Electrical properties

Frequency range	900 MHz
	2.4 GHz
	5 GHz
Impedance	50 $\Omega$

### Connection data

#### Connector connection

Connection method	SMA (male)
-------------------	------------

#### Connector connection

Connection method	SMA (male)
-------------------	------------

### Material specifications

Outer sheath, material	RADOX®(LSFH)
------------------------	--------------

### Cable/line

Cable length	50 cm
Cable type	EF 142
External cable diameter	5.00 mm
Outer sheath, material	RADOX®(LSFH)
External sheath, color	black
Bending radius, long-term	30.00 mm
868 / 900 MHz	0.3 dB
2.4 GHz	0.5 dB

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 70 °C

# RAD-PIG-EF142-PIPE - Adapter cable



2885922

<https://www.phoenixcontact.com/us/products/2885922>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)