

FL SWITCH SFNB 5TX - Industrial Ethernet Switch



2891001

<https://www.phoenixcontact.com/us/products/2891001>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ethernet switch, 5 TP RJ45 ports, automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), autocrossing function

Your advantages

- RJ45 ports support a transmission speed of 10/100 Mbps
- Local diagnostic indicators with LEDs
- Auto negotiation and autocrossing detection simplifies installation and setup

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2891001 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN19 |
| Product key | DNN113 |
| GTIN | 4046356457163 |
| Weight per piece (including packing) | 271 g |
| Weight per piece (excluding packing) | 263 g |
| Customs tariff number | 85176200 |
| Country of origin | TW |

FL SWITCH SFNB 5TX - Industrial Ethernet Switch



2891001

<https://www.phoenixcontact.com/us/products/2891001>

Technical data

Dimensions

| | |
|--------|--------|
| Width | 28 mm |
| Height | 110 mm |
| Depth | 70 mm |

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Material specifications

| | |
|------------------|----------------------------|
| Color (Housing) | white aluminium (RAL 9006) |
| Color (Cover) | anthracite gray (RAL 7016) |
| Housing material | Aluminum |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

Interfaces

Ethernet (RJ45)

| | |
|-------------------------------|-----------------------------------|
| Connection method | RJ45 |
| Note on the connection method | Auto negotiation and autocrossing |
| Transmission speed | 10/100 Mbps |
| Transmission physics | Ethernet in RJ45 twisted pair |
| Transmission length | 100 m (per segment) |
| Signal LEDs | Data receive, link status |
| No. of channels | 5 (RJ45 ports) |

Product properties

| | |
|----------------|--|
| Product type | Switch |
| Product family | Unmanaged Switch SFNB |
| Type | Block design |
| MTTF | 173.5 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%) |

Switch functions

| | |
|----------------------------------|---|
| Basic functions | Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode |
| MAC address table | 1k |
| Status and diagnostic indicators | LEDs: U _S , link and activity per port |
| Additional functions | Autonegotiation |

Security functions

FL SWITCH SFNB 5TX - Industrial Ethernet Switch



2891001

<https://www.phoenixcontact.com/us/products/2891001>

| | |
|-----------------|---|
| Basic functions | Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode |
|-----------------|---|

Electrical properties

| | |
|---|---|
| Local diagnostics | US Supply voltage Green LED |
| | LNK/ACT Link status/data transmission Green LED |
| | 100 Data transmission speed Yellow LED |
| Maximum power dissipation for nominal condition | 4.44 W |
| Transmission medium | Copper |

Supply

| | |
|-----------------------------|--|
| Supply voltage (DC) | 24 V DC |
| Supply voltage range | 12 V DC ... 48 V DC |
| Power supply connection | Via COMBICON, max. conductor cross-section 2.5 mm ² |
| Residual ripple | 3.6 V _{PP} (within the permitted voltage range) |
| Max. current consumption | 345 mA (at 12 V DC) |
| Typical current consumption | 185 mA (at U _S = 24 V DC) |

Connection data

| | |
|-----------------------------------|---|
| Connection method | Screw connection |
| pluggable | yes |
| Conductor cross-section, rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 30 ... 12 |
| Stripping length | 7 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -10 °C ... 60 °C |
| Ambient temperature (storage/transport) | -20 °C ... 85 °C |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |
| Air pressure (operation) | 86 kPa ... 108 kPa (up to 1500 m above sea level) |
| Air pressure (storage/transport) | 66 kPa ... 108 kPa (up to 3500 m above sea level) |

Approvals

Conformity/Approvals

| | |
|------------------|------------------------------------|
| UL, USA / Canada | Class I, Div. 2, Groups A, B, C, D |
|------------------|------------------------------------|

EMC data

| | |
|---------------------------------|---|
| Electromagnetic compatibility | Conformance with EMC Directive 2004/108/EC |
| Conformance with EMC directives | IEC 61000-6-2 IEC 61000-4-2 (ESD) Criterion B |
| | IEC 61000-4-3 (immunity to radiated interference) Criterion A |

FL SWITCH SFNB 5TX - Industrial Ethernet Switch



2891001

<https://www.phoenixcontact.com/us/products/2891001>

| | |
|----------------|--|
| | IEC 61000-4-4 (burst) Criterion B |
| | IEC 61000-4-5 (surge) Criterion B |
| | IEC 61000-4-6 (immunity to conducted interference) Criterion A |
| | IEC 61000-4-8 (immunity to magnetic fields) Criterion A |
| | EN 55022 (emitted interference) Criterion A |
| Noise immunity | EN 61000-6-2 |

Noise emission

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

System properties

Functionality

| | |
|-----------------|---|
| Basic functions | Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode |
|-----------------|---|

Signaling

| | |
|----------------|---|
| Status display | LEDs: U _S , link and activity per port |
|----------------|---|

FL SWITCH SFNB 5TX - Industrial Ethernet Switch



2891001

<https://www.phoenixcontact.com/us/products/2891001>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2891001>



IECEE CB Scheme

Approval ID: DK-88783-M1-UL



UL Listed

Approval ID: E238705



cUL Listed

Approval ID: E238705



KC

Approval ID: KCC-REI-PCK-FL289100



cUL Listed

Approval ID: E199827



UL Listed

Approval ID: E199827

FL SWITCH SFNB 5TX - Industrial Ethernet Switch



2891001

<https://www.phoenixcontact.com/us/products/2891001>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19170402 |
| ECLASS-15.0 | 19170402 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000734 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43222600 |
|-------------|----------|

2891001

<https://www.phoenixcontact.com/us/products/2891001>

Environmental product compliance

EU RoHS

| | |
|---|---------------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 15(a), 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-10 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | d7fb5d8e-21b7-48b1-8d08-ce67c6815f60 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 11.27 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com