

IBS USC4-2 - Masterboard

2812209

<https://www.phoenixcontact.com/us/products/2812209>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS Generation 4 masterboard

Commercial data

Item number	2812209
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR14
Product key	DRECAA
GTIN	4017918913991
Weight per piece (including packing)	40.367 g
Weight per piece (excluding packing)	40.367 g
Customs tariff number	85389091
Country of origin	DE

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Master module
Type of housing/design	Daughterboard

System properties

Module

Protocol chip	IBS IPMS 3
---------------	------------

Functionality

Number of I/O nodes	max. 4096 (8192 with coupling memory expansion)
---------------------	---

Electrical properties

IC power supply voltage	5 V DC \pm 10 % (DC)
-------------------------	------------------------

Supply

Typical current consumption	200 mA (without extensions)
-----------------------------	-----------------------------

Interfaces

INTERBUS

Connection method	Remote bus
-------------------	------------

User interface

Connection method	60-pos. basic connector and 40-pos. extension connector for power supply for -Diagnostics, -Configuration, -DPM interface, -Memory extension
-------------------	--

Dimensions

Width	50 mm
Length	70 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 70 °C
---------------------------------	----------------

IBS USC4-2 - Masterboard

2812209

<https://www.phoenixcontact.com/us/products/2812209>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2812209>



cULus Recognized
Approval ID: E140324

IBS USC4-2 - Masterboard

2812209

<https://www.phoenixcontact.com/us/products/2812209>



Classifications

ECLASS

ECLASS-13.0	27242605
ECLASS-15.0	27242605

ETIM

ETIM 10.0	EC001601
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	78d663a0-8266-42f8-83a1-9b4b7e3e9b54

EF3.1 Climate Change

CO2e kg	8.738 kg CO2e
---------	---------------