


IB IL 24 DO2-2A-2MBD - Inline terminal

2819053

<https://www.phoenixcontact.com/us/products/2819053>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the version IB IL 24 DO 2-2A

Inline digital output terminal, without accessories, 2 outputs, 24 V DC, 2 A, 2 Mbaud transmission speed, 4-conductor connection technology

Product description

The terminal is designed for use within an Inline station. It is used to output digital signals.

Your advantages

- Nominal current per output: 2 A
- Connection of actuators in 2-, 3-, and 4-conductor technology
- 2 digital outputs
- Diagnostic and status indicators
- Short-circuit and overload-protected outputs
- Total current of the terminal: 4 A

Commercial data

Item number	2819053
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRI132
GTIN	4017918876517
Weight per piece (including packing)	66.2 g
Weight per piece (excluding packing)	46 g
Customs tariff number	85389091
Country of origin	DE

IB IL 24 DO2-2A-2MBD - Inline terminal

2819053

<https://www.phoenixcontact.com/us/products/2819053>

Technical data

Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Material specifications

Color	green
-------	-------

Interfaces

Inline local bus

Connection method	Inline data jumper
Transmission speed	2 Mbps

System properties

Programming data

Length code (hex)	C2
ID code (dec.)	189
Length code (dec)	194
Process data channel	2 bit
Input address area	0 Byte
Output address area	2 bit
Parameter channel (PCP)	0 bit
Register length (bus)	2 bit

Output data

Digital:

Output name	Digital outputs
-------------	-----------------

IB IL 24 DO2-2A-2MBD - Inline terminal



2819053

<https://www.phoenixcontact.com/us/products/2819053>

Connection method	Spring-cage connection
Connection technology	2-, 3-, 4-conductor
Number of outputs	2
Protective circuit	Overload protection, short-circuit protection of outputs
Output voltage	24 V DC (via voltage jumper)
Maximum output current per channel	2 A
Maximum output current per module	4 A
Nominal output voltage	24 V DC (voltage difference at $I_{nom} \leq 1$ V)
Nominal load, inductive	48 W
Nominal load, lamp	48 W
Nominal load, ohmic	48 VA
Behavior with overload	Auto restart
Behavior with inductive overload	Output can be destroyed
Behavior at voltage switch-off	The output follows the power supply without delay

Product properties

Product type	I/O component
Product family	Inline
Type	modular Inline
No. of channels	2
Diagnostics messages	Short-circuit or overload of the digital outputs Error message in the diagnostic code (bus) and display (2 Hz) via the LED (D) on the module

Electrical properties

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 60 mA

Potentials: Segment circuit supply (U_S)

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 4 A

Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logics)/24 V supply (I/O)	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply (I/O) / functional ground	500 V AC, 50 Hz, 1 min

Connection data

Connection technology

IB IL 24 DO2-2A-2MBD - Inline terminal



2819053

<https://www.phoenixcontact.com/us/products/2819053>

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL 24 DO2-2A-2MBD - Inline terminal

2819053


<https://www.phoenixcontact.com/us/products/2819053>

Drawings

Dimensional drawing



Connection diagram



IB IL 24 DO2-2A-2MBD - Inline terminal



2819053

<https://www.phoenixcontact.com/us/products/2819053>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com