

IB IL TEMPCON 300 UTH-2MBD-PAC - Inline function terminal



2819833

<https://www.phoenixcontact.com/us/products/2819833>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline temperature controller, complete with accessories (connector and labeling field) with 8 thermocouple inputs, 8 binary outputs, 1 input for recording the total current of heating elements, expandable to 30 control circuits, transfer rate 2Mbaud.

Product description

Inline terminals with "2 MBD" added to their item designation work with a transmission speed of 2 Mbps. These terminal blocks are discontinued or no longer in the range. If you require this transmission speed, please ask your local Phoenix Contact representative. If you can work with a transmission speed of 500 kbps, select as a replacement the corresponding variant that does not have "2MBD" added to its item designation. Please note that a uniform transmission speed must always be used within one inline station.

Your advantages

- Transmission speed 2 Mbps
- Can be extended by up to 30 closed-loop control circuits using additional temperature measurement terminals.
- The Inline multi-channel temperature controller is a freely parameterizable slave for the Inline installation system.

Commercial data

Item number	2819833
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRI191
GTIN	4046356123099
Weight per piece (including packing)	260.3 g
Weight per piece (excluding packing)	260.3 g
Customs tariff number	85389091
Country of origin	DE

IB IL TEMPCON 300 UTH-2MBD-PAC - Inline function terminal



2819833

<https://www.phoenixcontact.com/us/products/2819833>

Technical data

Dimensions

Width	48.8 mm
Height	119.8 mm
Depth	71.5 mm

Interfaces

Inline local bus

Connection method	Inline data jumper
Transmission speed	2 Mbps

System properties

Module

ID code (dec.)	221
ID code (hex)	DD
Length code (hex)	06
Length code (dec)	06
Process data channel	32 bit
Input address area	4 Byte
Output address area	4 Byte
Register length	96 bit
Required parameter data	1 Byte
Required configuration data	5 Byte

Product properties

Product type	I/O component
Type	modular

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16

Environmental and real-life conditions

Ambient conditions

IB IL TEMPCON 300 UTH-2MBD-PAC - Inline function terminal



2819833

<https://www.phoenixcontact.com/us/products/2819833>

Degree of protection	IP20
----------------------	------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL TEMPCON 300 UTH-2MBD-PAC - Inline function terminal



2819833

<https://www.phoenixcontact.com/us/products/2819833>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com