

URELG 2 - Basic terminal block

2820262

<https://www.phoenixcontact.com/us/products/2820262>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows versions with a different no. of positions

Basic termination blocks with screw connection for NS 32 and NS 35/7.5 DIN rail, with end cover, for ST-REL..., ST-OV... and ST-OE... plugs, 2-pos.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2820262 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | C460 |
| Product key | DK61B4 |
| GTIN | 4017918076818 |
| Weight per piece (including packing) | 23.75 g |
| Weight per piece (excluding packing) | 21.528 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

URELG 2 - Basic terminal block

2820262

<https://www.phoenixcontact.com/us/products/2820262>

Technical data

Product properties

| | |
|---------------------|--------------|
| Product type | Relay socket |
| Number of positions | 2 |


Electrical properties

| | |
|-----------------------|--|
| Nominal voltage U_N | 400 V (voltage is determined by the coupling connector.) |
| Nominal current I_N | 16 A (current is determined by the coupling connector.) |

Connection data

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 9 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Dimensions

| | |
|---------------------|---|
| Dimensional drawing |  |
| Width | 14.6 mm (with cover) |
| Height | 42.5 mm |
| Depth | 112 mm |

Material specifications

| | |
|---------------------|-----------------|
| Color | gray (RAL 7042) |
| Insulating material | PA |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

URELG 2 - Basic terminal block


2820262

<https://www.phoenixcontact.com/us/products/2820262>



Drawings

Dimensional drawing



URELG 2 - Basic terminal block

2820262

<https://www.phoenixcontact.com/us/products/2820262>

Schematic diagram



- 1 = Coupling connector
- 2 = Coding
- 3 = Cover
- 4 = Basic termination block

URELG 2 - Basic terminal block



2820262

<https://www.phoenixcontact.com/us/products/2820262>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2820262>



EAC

Approval ID: RU C-DE.A*30.B.01742

URELG 2 - Basic terminal block



2820262

<https://www.phoenixcontact.com/us/products/2820262>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27371603 |
| ECLASS-15.0 | 27371603 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001456 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

URELG 2 - Basic terminal block



2820262

<https://www.phoenixcontact.com/us/products/2820262>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.135 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com