

FL SWITCH SFNT 7TX/FX-C - Industrial Ethernet Switch



2891046

<https://www.phoenixcontact.com/us/products/2891046>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wide-temperature Ethernet switch, 7 TP RJ45 ports, 1 FO port, 100 Mbps full duplex in SC-D format, automatic detection of data transmission speed of 10/100 Mbps (RJ45), autocrossing function, autocrossing function, reads QoS priority messages, accepts security frames. Conformal coating for harsh environments.

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2891046 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | DN19 |
| Product key | DNN113 |
| GTIN | 4046356651110 |
| Weight per piece (including packing) | 640.1 g |
| Weight per piece (excluding packing) | 470 g |
| Customs tariff number | 85176200 |
| Country of origin | TW |

FL SWITCH SFNT 7TX/FX-C - Industrial Ethernet Switch



2891046

<https://www.phoenixcontact.com/us/products/2891046>

Technical data

Dimensions

| | |
|--------|--------|
| Width | 50 mm |
| Height | 130 mm |
| Depth | 100 mm |

Material specifications

| | |
|------------------|----------|
| Housing material | Aluminum |
|------------------|----------|

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

Interfaces

Ethernet (RJ45)

| | |
|-------------------------------|-----------------------------------|
| Connection method | RJ45 |
| Note on the connection method | Auto negotiation and autocrossing |
| Transmission speed | 10/100 Mbps |
| Transmission physics | Ethernet in RJ45 twisted pair |
| Transmission length | 100 m (per segment) |
| Signal LEDs | Data receive, link status |
| No. of channels | 7 (RJ45 ports) |

Fiber optic interface

| | |
|----------------------|---|
| Connection method | SC |
| Transmission speed | 100 Mbps (full duplex) |
| Transmission physics | multi-mode fiberglass |
| Transmission length | 12.1 km (fiberglass with F-G 62.5/125 0.7 dB/km F1000) 3.3 km (fiberglass with F-G 62.5/125 2.6 dB/km F600) 7.1 km (fiberglass with F-G 50/125 0.7 dB/km F1200) 3.1 km (fiberglass with F-G 50/125 1.6 dB/km F800) |
| Wavelength | 1300 nm |
| No. of channels | 1 (SC multi-mode) |

Product properties

| | |
|----------------|---|
| Product type | Switch |
| Product family | Unmanaged Switch SFNT |
| Type | Block design |
| MTTF | 63.4 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%) |

Switch functions

| | |
|-----------------|--|
| Basic functions | Unmanaged switch / autonegotiation, complies with IEEE 802.3, store and forward switching mode, includes QoS and alarm contact |
|-----------------|--|

FL SWITCH SFNT 7TX/FX-C - Industrial Ethernet Switch



2891046

<https://www.phoenixcontact.com/us/products/2891046>

| | |
|----------------------------------|--|
| Status and diagnostic indicators | LEDs: U _{S1} , U _{S2} (redundant voltage supply), link and activity per port |
| Additional functions | Autonegotiation |
| Security functions | |
| Basic functions | Unmanaged switch / autonegotiation, complies with IEEE 802.3, store and forward switching mode, includes QoS and alarm contact |

Electrical properties

| | |
|---|---|
| Local diagnostics | US1/2 Supply voltage Green LED |
| | LNK/ACT Link status/data transmission Green LED |
| | 100 Data transmission speed Yellow LED |
| Maximum power dissipation for nominal condition | 4.35 W |
| Transmission medium | Copper |
| | FO |

Supply

| | |
|-----------------------------|--|
| Supply voltage (DC) | 24 V DC (redundant) |
| Supply voltage range | 9 V DC ... 32 V DC |
| Power supply connection | Via COMBICON, max. conductor cross-section 2.5 mm ² |
| Residual ripple | 3.6 V _{PP} (within the permitted voltage range) |
| Max. current consumption | 565 mA (@9 V DC) |
| Typical current consumption | 180 mA (at U _S = 24 V DC) |

Connection data

| | |
|-----------------------------------|---|
| Conductor cross-section, rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible | 2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 14 |
| Stripping length | 7 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 75 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |
| Air pressure (operation) | 62 kPa ... 108 kPa (up to 4160 m above mean sea level) |
| Air pressure (storage/transport) | 62 kPa ... 108 kPa (up to 4160 m above mean sea level) |

Approvals

Conformity/Approvals

| | |
|-------------|-----------------------------|
| Conformance | CE-compliant |
| ATEX | Ⓜ II 3 G Ex nA nC IIC T4 Gc |

FL SWITCH SFNT 7TX/FX-C - Industrial Ethernet Switch



2891046

<https://www.phoenixcontact.com/us/products/2891046>

| | |
|---------------------------------|------------------------------------|
| EU-type examination certificate | DEMKO 16 ATEX 1617X |
| IECEEx | Ex nA nC IIC T4 Gc |
| IECEEx certificate | IECEEx UL 16.0093X |
| UL, USA / Canada | Class I, Div. 2, Groups A, B, C, D |

EMC data

| | |
|-------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC Directive 2004/108/EC |
| Noise immunity | EN 61000-6-2 |

Noise emission

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

System properties

Functionality

| | |
|-----------------|--|
| Basic functions | Unmanaged switch / autonegotiation, complies with IEEE 802.3, store and forward switching mode, includes QoS and alarm contact |
|-----------------|--|

Signaling

| | |
|----------------|--|
| Status display | LEDs: U _{S1} , U _{S2} (redundant voltage supply), link and activity per port |
|----------------|--|

FL SWITCH SFNT 7TX/FX-C - Industrial Ethernet Switch



2891046

<https://www.phoenixcontact.com/us/products/2891046>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43222600 |
|-------------|----------|

FL SWITCH SFNT 7TX/FX-C - Industrial Ethernet Switch



2891046

<https://www.phoenixcontact.com/us/products/2891046>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-10 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com