

# ST-REL3-HW 42/21 - Relay connectors



2821067

<https://www.phoenixcontact.com/us/products/2821067>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay connector, equipped with Hengstler miniature round relay, contacts (AgCdO+Au): small to large loads, 1 changeover contact, input voltage 42 V AC, with LED display, pluggable into basic terminal blocks

The figure shows version ST-REL3-HG 24/21

## Commercial data

Item number	2821067
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DK6123
GTIN	4017918076986
Weight per piece (including packing)	61.35 g
Weight per piece (excluding packing)	60 g
Customs tariff number	85364190
Country of origin	DE

# ST-REL3-HW 42/21 - Relay connectors



2821067

<https://www.phoenixcontact.com/us/products/2821067>

## Technical data

### Product properties

Product type	Relay Module
Operating mode	100% operating factor
Mechanical service life	approx. $10^7$ cycles

### Data management status

Date of last data management	01.04.2026
------------------------------	------------

### Electrical properties

Test voltage (Winding/contact)	2 kV AC (50 Hz, 1 min., winding/contact)
--------------------------------	--

### Input data

#### Coil side

Nominal input voltage $U_N$	42 V AC
Input voltage range	33.6 V AC ... 46.2 V AC
Input voltage range in reference to $U_N$	0.8 ... 1.1
Typical input current at $U_N$	50 mA
Typical response time	4 ms ... 15 ms (depending on phase relation)
Typical release time range	4 ms ... 15 ms (depending on phase relation)
Operating voltage display	yes

### Output data

#### Switching

Contact switching type	Single contact, 1 changeover contact
Type of switch contact	Single contact
Contact material	AgCdO, hard gold-plated
Maximum switching voltage	250 V AC/DC
Limiting continuous current	6 A
Maximum inrush current	6 A
Interrupting rating (ohmic load) max.	120 W (at 24 V DC)
	180 W (at 48 V DC)
	105 W (at 60 V DC)
	60 W (at 110 V DC)
	90 W (at 220 V DC)
	1500 VA (for 250 V AC)

### Connection data

Connection method	Plug-in connection
-------------------	--------------------

### Dimensions

Width	20.8 mm
-------	---------

# ST-REL3-HW 42/21 - Relay connectors



2821067

<https://www.phoenixcontact.com/us/products/2821067>

Height	33 mm
Depth	66.5 mm

## Material specifications

Color	transparent
-------	-------------

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	DIN VDE 0110b, Gr. C for 250 V DC
	DIN VDE 0160 (in relevant parts)

## Mounting

Mounting type	Plug-in mounting
---------------	------------------

# ST-REL3-HW 42/21 - Relay connectors

2821067

<https://www.phoenixcontact.com/us/products/2821067>

## Drawings

Circuit diagram



# ST-REL3-HW 42/21 - Relay connectors



2821067

<https://www.phoenixcontact.com/us/products/2821067>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)