

FL SWITCH 3012E-2SFX - Industrial Ethernet Switch



2891067

<https://www.phoenixcontact.com/us/products/2891067>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Managed Ethernet switch meets IEC 61850-3 and IEEE 1613 standards. Provides 12 RJ45 ports at 10/100 Mbps and two SFP slots at 100 Mbps) with an operating temperature of -40°C ... +70°C.

Product description

FL SWITCH 3000 managed industrial Ethernet switches combine extensive network performance and security features with complete IEEE redundancy (STP/RSTP/MST) and 15 ms recovery time extended ring redundancy. Unique web customization provides a simplified user interface for today's applications and scalable functionality for future needs. A comprehensive mix of fiber optic and copper port connections meets a wide range of applications.

Your advantages

- Network structure according to IEC 61850
- IEEE 1613

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2891067 |
| Packing unit | 1 pc |
| Sales key | DN17 |
| Product key | DNN125 |
| GTIN | 4046356773676 |
| Weight per piece (including packing) | 1,634.6 g |
| Weight per piece (excluding packing) | 1,626.1 g |
| Customs tariff number | 85176200 |
| Country of origin | TW |

FL SWITCH 3012E-2SFX - Industrial Ethernet Switch



2891067

<https://www.phoenixcontact.com/us/products/2891067>

Technical data

Dimensions

| | |
|--------|---------|
| Width | 78.6 mm |
| Height | 145 mm |
| Depth | 125 mm |

Material specifications

| | |
|------------------|----------|
| Housing material | Aluminum |
|------------------|----------|

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

Interfaces

Ethernet (RJ45)

| | |
|-------------------------------|-----------------------------------|
| Connection method | RJ45 |
| Note on the connection method | Auto negotiation and autocrossing |
| Transmission speed | 10/100 Mbps |
| Transmission physics | Ethernet in RJ45 twisted pair |
| Transmission length | 100 m |
| No. of channels | 12 (RJ45 ports) |

Fiber optic interface

| | |
|----------------------|--|
| Connection method | SFP |
| Transmission speed | 100 Mbps (full duplex) |
| Transmission physics | Depending on the SFP module |
| Transmission length | up to 40 km (Depending on the fiber/SFP module used) |
| No. of channels | 2 (SFP ports) |

Product properties

| | |
|----------------|--|
| Product type | Switch |
| Product family | Managed Switch 3000 |
| Type | Block design |
| MTTF | 35.21 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%) |

Switch functions

| | |
|----------------------------------|--|
| Basic functions | Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts |
| Signal contact control voltage | 24 V DC |
| Signal contact control current | 100 mA |
| Redundancy | ERR (Extended ring redundancy) |
| Status and diagnostic indicators | LEDs: U _{S1} , U _{S2} (redundant voltage supply), link and activity per port |

FL SWITCH 3012E-2SFX - Industrial Ethernet Switch



2891067

<https://www.phoenixcontact.com/us/products/2891067>

Security functions

| | |
|-----------------|--|
| Basic functions | Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts |
|-----------------|--|

Electrical properties

| | |
|---|--|
| Local diagnostics | US1, US2 Supply voltage Green LED LNK/ACT Link status/data transmission Green LED |
| Maximum power dissipation for nominal condition | 7.49 W |
| Test section | Supply voltage/functional ground 500 V 1 min |
| Transmission medium | Copper |

Supply

| | |
|-----------------------------|--|
| Supply voltage (DC) | 24 V DC (redundant) |
| Supply voltage range | 12 V DC ... 48 V DC |
| Residual ripple | 3.6 V _{PP} (within the permitted voltage range) |
| Typical current consumption | 312 mA (at U _S = 24 V DC) |

Function

| | |
|--------------------------------|---------|
| Signal contact control voltage | 24 V DC |
| Signal contact control current | 100 mA |

Connection data

Power supply

| | |
|-----------------------------------|---|
| Connection method | Screw connection |
| pluggable | yes |
| Conductor cross-section, rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Stripping length | 7 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |
| Air pressure (operation) | 57 kPa ... 108 kPa (up to 4850 m above mean sea level) |
| Air pressure (storage/transport) | 57 kPa ... 108 kPa (up to 4850 m above mean sea level) |

Approvals

Conformity/Approvals

FL SWITCH 3012E-2SFX - Industrial Ethernet Switch



2891067

<https://www.phoenixcontact.com/us/products/2891067>

| | |
|-------------|--------------|
| Conformance | CE-compliant |
|-------------|--------------|

EMC data

| | |
|----------------|--|
| Noise immunity | IEC 61850-3, IEEE 1613, EN 61000-6-2: 2005 |
|----------------|--|

Noise emission

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

System properties

Functionality

| | |
|-----------------|--|
| Basic functions | Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts |
|-----------------|--|

Signaling

| | |
|----------------|--|
| Status display | LEDs: U _{S1} , U _{S2} (redundant voltage supply), link and activity per port |
|----------------|--|

FL SWITCH 3012E-2SFX - Industrial Ethernet Switch



2891067

<https://www.phoenixcontact.com/us/products/2891067>

Classifications

ECLASS

ECLASS-13.0

19170401

ETIM

ETIM 9.0

EC000734

UNSPSC

UNSPSC 21.0

43222600

2891067

<https://www.phoenixcontact.com/us/products/2891067>

Environmental product compliance

EU RoHS

| | |
|---|---------------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 15(a), 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-10 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com