

# ST-REL2-KG 48/1 - Relay connectors



2823638

<https://www.phoenixcontact.com/us/products/2823638>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay connector, fitted with miniature switching relay, contacts (AgNi): Medium to large loads, 1 N/O contact, 48 V AC/DC input voltage, with light indicator, can be plugged into basic terminal blocks

The figure shows version ST-REL 2-KG 24/1

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2823638                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | C460                           |
| Product key                          | DK6122                         |
| GTIN                                 | 4017918077471                  |
| Weight per piece (including packing) | 35.14 g                        |
| Weight per piece (excluding packing) | 35.14 g                        |
| Customs tariff number                | 85364190                       |
| Country of origin                    | DE                             |

# ST-REL2-KG 48/1 - Relay connectors



2823638

<https://www.phoenixcontact.com/us/products/2823638>

## Technical data

### Product properties

|                         |                                |
|-------------------------|--------------------------------|
| Product type            | Relay Module                   |
| Operating mode          | 100% operating factor          |
| Mechanical service life | approx. $2 \times 10^7$ cycles |

### Data management status

|                              |            |
|------------------------------|------------|
| Date of last data management | 12.09.2025 |
|------------------------------|------------|

### Electrical properties

|   |  |
|---|--|
| Maximum power dissipation for nominal condition | 0.41 W                                     |
| Test voltage (Winding/contact)                  | 2.5 kV AC (50 Hz, 1 min., winding/contact) |

### Input data

#### Coil side

|   |                               |
|---|-------------------------------|
| Nominal input voltage $U_N$               | 48 V AC/DC                    |
| Input voltage range                       | 43.2 V AC/DC ... 52.8 V AC/DC |
| Input voltage range in reference to $U_N$ | 0.9 ... 1.1                   |
| Drive and function                        | monostable                    |
| Typical input current at $U_N$            | 8.5 mA                        |
| Typical response time                     | 10 ms (with DC)               |
| Typical release time                      | 10 ms (with DC)               |
| Protective circuit                        | Bridge rectifier, varistor    |
| Operating voltage display                 | yes                           |

### Output data

#### Switching

|                                       |   |
|---------------------------------------|---|
| Contact switching type                | Single contact, 1 N/O contact   |
| Type of switch contact                | Single contact  |
| Contact material                      | AgNi  |
| Maximum switching voltage             | 250 V AC/DC   |
| Limiting continuous current           | 6 A   |
| Maximum inrush current                | 8 A   |
| Interrupting rating (ohmic load) max. | 95 W (at 24 V DC)<br>50 W (at 48 V DC)<br>45 W (at 60 V DC)<br>45 W (at 110 V DC)<br>75 W (at 220 V DC)<br>1500 VA (for 250 V AC) |

### Dimensions

|       |         |
|-------|---------|
| Width | 14.6 mm |
|-------|---------|

# ST-REL2-KG 48/1 - Relay connectors



2823638

<https://www.phoenixcontact.com/us/products/2823638>

|        |         |
|--------|---------|
| Height | 33 mm   |
| Depth  | 66.5 mm |

## Material specifications

|       |                  |
|-------|------------------|
| Color | green (RAL 6021) |
|-------|------------------|

## Environmental and real-life conditions

### Ambient conditions

|   |                  |
|---|------------------|
| Ambient temperature (operation)         | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

## Standards and regulations

|                       |  |
|-----------------------|--|
| Standards/regulations | DIN VDE 0110b, Gr. C for 250 V DC          |
|                       | IEC 60255/DIN VDE 0435 (in relevant parts) |
|                       | DIN EN 50178/VDE 0160 (in relevant parts)  |
|                       | EN 60730/DIN VDE 0631                      |
|                       | DIN VDE 0160 (in relevant parts)           |

## Mounting

|               |                  |
|---------------|------------------|
| Mounting type | Plug-in mounting |
|---------------|------------------|

# ST-REL2-KG 48/1 - Relay connectors


2823638

<https://www.phoenixcontact.com/us/products/2823638>



## Drawings

Circuit diagram



# ST-REL2-KG 48/1 - Relay connectors



2823638

<https://www.phoenixcontact.com/us/products/2823638>

## Classifications

### UNSPSC

UNSPSC 21.0

39122334

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)