

ST-REL4-KG 24/S/1 - Relay connectors



2826693

<https://www.phoenixcontact.com/us/products/2826693>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay connector, fitted with miniature switching relay and integrated manual switch, contacts (AgNi): Medium to large loads, 1 N/O contact, 24 V AC/DC input voltage, with light indicator, can be plugged into basic terminal blocks

Commercial data

Item number	2826693
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK6182
GTIN	4017918078010
Weight per piece (including packing)	56.37 g
Weight per piece (excluding packing)	56 g
Customs tariff number	85364190
Country of origin	DE

ST-REL4-KG 24/S/1 - Relay connectors



2826693

<https://www.phoenixcontact.com/us/products/2826693>

Technical data

Product properties

Product type	Relay Module
Mechanical service life	> 10 ⁷ cycles

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Data management status

Date of last data management	12.09.2025
------------------------------	------------

Electrical properties

Maximum power dissipation for nominal condition	0.48 W
Test voltage (Winding/contact)	2.5 kV AC (50 Hz, 1 min., winding/contact)

Input data

Coil side

Nominal input voltage U _N	24 V AC/DC
Input voltage range	19.2 V AC/DC ... 26.4 V AC/DC
Input voltage range in reference to U _N	0.8 ... 1.1
Drive and function	monostable
Typical input current at U _N	20 mA
Typical response time	4 ms ... 10 ms
Typical release time range	4 ms ... 10 ms
Protective circuit	Bridge rectifier; Bridge rectifier Varistor; Varistor
Operating voltage display	Yellow LED
Coil resistance	1200 Ω ±15 %

Output data

Switching

Contact switching type	Single contact, 1 N/O contact
Type of switch contact	Single contact
Contact material	AgNi
Maximum switching voltage	220 V AC
Limiting continuous current	3 A
Maximum inrush current	15 A
Interrupting rating (ohmic load) max.	750 VA

Connection data

Connection method	Plug-in connection
-------------------	--------------------

ST-REL4-KG 24/S/1 - Relay connectors



2826693

<https://www.phoenixcontact.com/us/products/2826693>

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

Standards and regulations

Standards/regulations	VDE 0110
-----------------------	----------

Mounting

Mounting type	Plug-in mounting
Mounting position	any

ST-REL4-KG 24/S/1 - Relay connectors



2826693

<https://www.phoenixcontact.com/us/products/2826693>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com