

FL SWITCH SFN 5GT - Industrial Ethernet Switch



2891444

<https://www.phoenixcontact.com/us/products/2891444>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ethernet switch, five TP-RJ45 ports with 10/100/1000 Mbps on all ports, automatic detection of data transmission speed of 10/100/1000 Mbps (RJ45), autocrossing function, and QoS.

Product description

The FL SWITCH SFN... range of Factoryline switches with standard functions in numerous versions can be used for quick and cost-effective Ethernet network expansion to the field level. Due to their narrow housing design, the components are suitable for universal remote use in control cabinets and junction boxes. The switches have five or eight ports.

The FL SWITCH SFN 5GT support the auto negotiation function at the twisted pair ports and offer transmission speeds of 10/100/1000 Mbps. Mixed operation for the connection of segments with different data transmission speeds is also supported.

The RJ45 ports offer an auto crossing function, which means it is not necessary to make a distinction between 1:1 and crossover cables.

Switching properties

-Multi-address function

The switch independently learns the addresses for termination devices. The switch can store up to 8192 MAC addresses in its address table.

-Quality of service

In case of heavy traffic, packets tagged with higher priority 802.1Q or Differentiated Services values will be given preference. The switch has four internal priority queues.

-Multicast filtering

The multicast filter will block PROFINET PTCP-Delay traffic. This is accomplished by filtering frames with the destination MAC address in the range 01-80-C2-00-00-02 through 01-80-C2-00-00-0F. Note that the filter blocks LLDP traffic because PTCP-Delay uses the same MAC address, 01-80-C2-00-00-0E.

Power connection is via a removable COMBICON connector. US is 24 V DC and GND is 0 V DC. ⚡ FE, functional earth.

Your advantages

- QoS-prioritized (Quality of Service) messages
- Jumbo frame support (frame size up to 10,240 bytes/frame)
- All ports offer transmission speeds of 1000 Mbps
- Local diagnostic indicators with LEDs
- Auto negotiation and autocrossing detection simplifies installation and setup

Commercial data

Item number	2891444
Packing unit	1 pc
Sales key	DN19
Product key	DNN113

FL SWITCH SFN 5GT - Industrial Ethernet Switch



2891444

<https://www.phoenixcontact.com/us/products/2891444>

GTIN	4055626000886
Weight per piece (including packing)	303.7 g
Weight per piece (excluding packing)	205 g
Customs tariff number	85176200
Country of origin	TW

FL SWITCH SFN 5GT - Industrial Ethernet Switch



2891444

<https://www.phoenixcontact.com/us/products/2891444>

Technical data

Dimensions

Width	28 mm
Height	110 mm
Depth	70 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Material specifications

Housing material	Aluminum
------------------	----------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Interfaces

Ethernet (RJ45)

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100/1000 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
No. of channels	5 (RJ45 ports)

Product properties

Product type	Switch
Product family	Unmanaged Switch SFN
Type	Block design
MTTF	205.1 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Switch functions

Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode
PROFINET conformance class	Conformance Class A
Status and diagnostic indicators	LEDs: U _S , link and activity per port
Additional functions	Autonegotiation Jumbo frames (max. 10240 bytes)

Security functions

Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3,
-----------------	--

FL SWITCH SFN 5GT - Industrial Ethernet Switch



2891444

<https://www.phoenixcontact.com/us/products/2891444>

store and forward switching mode

Electrical properties

Maximum power dissipation for nominal condition	4.8 W
Transmission medium	Copper

Supply

Supply voltage (DC)	24 V DC
Supply voltage range	10 V DC ... 60 V DC
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Max. current consumption	580 mA (10 V DC)
Typical current consumption	200 mA (at U _S = 24 V DC)

Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-10 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Air pressure (operation)	62 kPa ... 108 kPa (up to 4850 m above mean sea level)
Air pressure (storage/transport)	62 kPa ... 108 kPa (up to 4850 m above mean sea level)

EMC data

Noise immunity	EN 61000-6-2:2005
----------------	-------------------

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

System properties

Functionality

Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode
-----------------	---

Signaling

Status display	LEDs: U _S , link and activity per port
----------------	---

FL SWITCH SFN 5GT - Industrial Ethernet Switch




2891444


<https://www.phoenixcontact.com/us/products/2891444>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2891444>

 **KC**
Approval ID: R-REI-PCK-2891444

 **cUL Listed**
Approval ID: E199827

 **UL Listed**
Approval ID: E199827

FL SWITCH SFN 5GT - Industrial Ethernet Switch



2891444

<https://www.phoenixcontact.com/us/products/2891444>

Classifications

ECLASS

ECLASS-13.0	19170402
ECLASS-15.0	19170402

ETIM

ETIM 10.0	EC000734
-----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

FL SWITCH SFN 5GT - Industrial Ethernet Switch



2891444

<https://www.phoenixcontact.com/us/products/2891444>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	cf84feb8-0e68-4f8c-bbee-1929266b85f7

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com